

42V Input Standoff Voltage, 1A Step-Down Converter in SOT23-6

DESCRIPTION

The ETA2842 is a wide input range, high-efficiency, and high frequency DC-to-DC step-down switching regulator, capable of delivering up to IA of output current. With a fixed switching frequency of 650KHz, this current mode PWM controlled converter allows the use of small external components, such as ceramic input and output caps, as well as small inductors.ETA2842 also employs a proprietary control scheme that switches the device into a power save mode during light load, thereby extending the range of high efficiency operation. An OVP function protects the IC itself and its downstream system against input voltage surges. With this OVP function, the IC can stand off input voltage as high as 42V, making it an ideal solution for industrial applications such as smart meters as well as automotive applications.

In automotive systems, power comes from the battery, with its voltage typically between 9V and 24V. Including cold crank and double battery jump-starts, the minimum input voltage may be as low as 4V and the maximum up to 36V, with even higher transient voltages. With these high input voltages, linear regulators cannot be used for high supply currents without overheating the regulator. Instead, high efficiency switching regulators such as ETA2842 must be used to minimize thermal dissipation.

ETA2842 is available SOT23-6 Packages.

FFATURES

- Wide Input Operating Range from 4V to 38V
- Standoff Input Voltage: 42V
- Output up to 12V
- High Efficiency at 12V In 5V Out: Up to 91%:
- High Efficiency PFM mode at light load
- Capable of Delivering 1A
- No External Compensation Needed
- Current Mode control
- Logic Control Shutdown
- Thermal shutdown and UVLO
- Available in SOT23-6 Package


APPLICATIONS


- Smart Meters
- Industrial Applications
- Automotive Applications

ORDERING INFORMATION

PART#	PACKAGE PIN	TOP MARK	
ETA2842S2G	SOT23-6	EGYW Date Code Product Number	

TYPICAL APPLICATION






Outperform with Efficiency



PIN CONFIGURATION



ABSOLUTE MAXIMUM RATINGS

ELECTRICAL CHACRACTERISTICS

(V_{IN} = 12V, unless otherwise specified. Typical values are at T_{A} = $25^{\circ}\text{C.})$

PARAMETER	CONDITIONS	MIN	TYP	MAX	ZTINU
Input Standoff Voltage		42			V
Input Voltage Range		4		38	V
Input UVLO	Rising, Hysteresis=140mV		3.80		V
Input OVP	Rising, Hysteresis=1.3V		38		V
Input Supply Current	V _{FB} = 0.85V	0.6		mA	
Input Shutdown Current		6		μА	
FB Feedback Voltage	lback Voltage 0.800			٧	
FB Input Current	ent 0.01			μА	
Switching Frequency		650		KHz	
Maximum Duty Cycle		90			%
FoldBack Frequency	$V_{FB} = \square V$		60		KHz
High side Switch On Resistance	gh side Switch On Resistance Isw = 200mA 400			mΩ	
High side Switch Current Limit			1.2		A
SW Leakage Current	V _{IN} =12V,V _{SW} =0, EN= GND			10	μА
EN Input Current	V _{IN} =12V ,V _{EN} =5V		1	5	μА
EN Input Low Voltage	Rising, Hysteresis=100mV	0.8	1.1	1.4	V
Thermal Shutdown	Hysteresis=40°C		150		<u>оС</u>


PIN DESCRIPTION


PIN #	NAME	DESCRIPTION
1	BST	Bootstrap pin. Connect a 10nF capacitor from this pin to SW
2	GND	Ground
3	FB	Feedback Input. Connect an external resistor divider from the output to FB and GND to set $V_{ ext{OUT}}$
4	EN	Enable pin for the IC. Drive this pin high to enable the part, low to disable.
5	IN	Supply Voltage. Bypass with a 10µF ceramic capacitor to GND
6	SM	Inductor Connection. Connect an inductor Between SW and the regulator output.





TYPICAL CHARACTERISTICS


(Typical values are at $T_A=25\,^{\circ}\text{C}$ unless otherwise specified.)





















TYPICAL CHARACTERISTICS

(Typical values are at $T_A=25\,^{\circ}\text{C}$ unless otherwise specified.)


Start-up Waveform with EN VIN=12 V, VOUT=5 V, IOUT=0 A




Start-up Waveform with EN=V_{IN} V_{IN}=12V,V_{OUT}=5V,I_{OUT}=0A




Shutdown Waveform with EN VIN=30V, VOUT=5V, IOUT=0.5A




Switching Waveform VIN=12 V, VOUT=5 V, LOUT=0.1A




Switching Waveform




Load Transient Response




Load Transient Response
VIN=12 V, VOUT=5 V, IOUT=0 to 0.5A



Short-Circuit Response V_{IN}=24V,V_{OUT}=5V,I_{OUT}=0A to Short



Short-Circuit Recovery
VIN=24V, VOUT=5V, IOUT= Short to DA





FUNCTIONAL DESCRIPTIONS


Loop Operation

The ETA2842 is a wide input range, high-efficiency, DC-to-DC step-down switching regulator, capable of delivering up to 1A of output current, integrated with a $400m\Omega$ high side MOSFET. It uses a PWM current-mode control scheme. An error amplifier integrates error between the FB signal and the internal reference voltage. The output of the integrator is then compared to the sum of a current-sense signal and the slope compensation ramp. This operation generates a PWM signal that modulates the duty cycle of the power MOSFETs to achieve regulation for output voltage.

Light Load Operation

Traditionally, a fixed constant frequency PWM DC-DC regulator always switches even when the output load is small. When energy is shuffling back and forth through the power MOSFETs, power is lost due to the finite RDSONs of the MOSFETs and parasitic capacitances. At light load, this loss is prominent and efficiency is therefore very low. ETA2842 employs a proprietary control scheme that improves efficiency in this situation by enabling the device into a power save mode during light load, thereby extending the range of high efficiency operation.

BLOCK DIAGRAM





APPLICATION INFORMATION

Setting Output Voltages

Output voltages are set by external resistors. The FB threshold is $\Omega.8V.$

$$R_{TOP} = R_{BOTTOM} \times [(V_{OUT} / 0.8) - 1]$$

Inductor Selection

The peak-to-peak ripple is limited to 30% of the maximum output current. This places the peak current far enough from the minimum overcurrent trip level to ensure reliable operation while providing enough current ripples for the current mode converter to operate stably. In this case, for 1A maximum output current, the maximum inductor ripple current is 300 mA. The inductor size is estimated as following equation:

LIDEAL=(VIN(MAX)-VOUT)/IRIPPLE*DMIN*(1/FOSC)

Therefore, for Vniit=5V.

The inductor values is calculated to be $L = 13\mu H$.

Chose 10µH or 15µH

For $V_{DUT} = 3.3V$,

The inductor values is calculated to be $L = 9.2\mu H$.

Chose 10uH

Output Capacitor Selection

For most applications a nominal $22\mu F$ or larger capacitor is suitable. The ETA2842 internal compensation is designed for a fixed corner frequency that is equal to

$$FC = \frac{1}{2 * \pi \sqrt{COUT * L}} = 8.7 \text{Khz}$$

For example, for Vout=5V, L=15µH, Cout=22µF.

The output capacitor keeps output ripple small and ensures control-loop stability. The output capacitor must also have low impedance at the switching frequency. Ceramic, polymer, and tantalum capacitors are suitable, with ceramic exhibiting the lowest ESR and high-frequency impedance. Output ripple with a ceramic output capacitor is approximately as follows:

 $V_{RIPPLE} = IL_{(PEAK)}[1 / (2\pi \times f_{OSC} \times C_{OUT})]$

If the capacitor has significant ESR, the output ripple component due to capacitor ESR is as follows:

 $V_{RIPPLE(ESR)} = IL_{(PEAK)} \times ESR$

Input Capacitor Selection


The input capacitor in a DC-to-DC converter reduces current peaks drawn from the battery or other input power source and reduces switching noise in the controller. The impedance of the input capacitor at the switching frequency should be less than that of the input source so high-frequency switching currents do not pass through the input source. The output capacitor keeps output ripple small and ensures control-loop stability.


Components Selection


V _{DUT} (V)	Cουτ (μF)	L (µH)
8	22	15 to 22
5	22	10 to 15
3.3	22	6.8 to 10



PACKAGE OUTLINE







Symbol	Dimensions Ir	n Millimeters	Dimensions	s In Inches	
	Min	Max	Min	Max	
Α	1.050	1.250	0.041	0.049	
A1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.820	3.020	0.111	0.119	
E	1.500	1.700	0.059	0.067	
E1	2.650	2.950	0.104	0.116	
е	0.950(BSC)		0.037(BSC)		
e1	1.800	2.000	0.071	0.079	
L	0.300	0.600	0.012	0.024	
θ	0°	8°	0°	8°	