

# RN73C1J200KBDT ✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 1879207-1

200K  $\Omega$ , Thin Film, Precision Resistor, .1 %, 2 Termination, 0603, Taped & Reeled, .063 W,  $\pm 10$  ppm/ $^{\circ}\text{C}$ , Solder, Height .018 in [.45 mm], Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0603**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

## Features

### Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0603
Element Type	Thin Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Operating Voltage	50 V
Passive Component Tolerance	.1 %
Resistance Class	1k $\Omega$ – 1M $\Omega$
Resistance Value	200K $\Omega$
Power Rating	.063 W

### Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



### Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

### Usage Conditions

Temperature Coefficient	$\pm 10$ ppm/ $^{\circ}$ C
-------------------------	----------------------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2-1879207-1  
RN 0603 324K 0.1% 10PPM 5K RL



TE Part # 1879207-2  
RN 0603 205K 0.1% 10PPM 5K RL



TE Part # 1879140-7  
RN 0603 21K5 0.1% 10PPM 5K RL

### Also in the Series | Holsworthy RN73



Surface Mount Resistors(3788)

### Customers Also Bought



TE Part #8-1879140-9  
RN 0603 154K 0.1% 10PPM 5K RL



TE Part #9-1879140-9  
RN 0603 196K 0.1% 10PPM 5K RL



TE Part #1-1879207-0  
RN 0603 249K 0.1% 10PPM 5K RL



TE Part #1-1879207-9  
RN 0603 309K 0.1% 10PPM 5K RL



TE Part #1879207-2  
RN 0603 205K 0.1% 10PPM 5K RL



TE Part #1-1879207-7  
RN 0603 294K 0.1% 10PPM 5K RL



TE Part #6-2176391-7  
RQ 1206 60K4 0.1% 10PPM 5K RL



TE Part #1879207-3  
RN 0603 210K 0.1% 10PPM 5K RL



TE Part #2-1879207-0  
RN 0603 316K 0.1% 10PPM 5K RL



TE Part #9-1879140-7  
RN 0603 187K 0.1% 10PPM 5K RL



## Documents

### Product Drawings

[RN 0603 200K 0.1% 10PPM 5K RL](#)

English

---

### Datasheets & Catalog Pages

[High Precision Resistors \(SMD\) - Type RN73 Series - Tyco Electronics Passives](#)

English