



MC5404 • MC7404

2



ORIG

004468

4468

MOT


Add Suffix F for TO-86 ceramic package (Case 607).
 Suffix L for TO-116 ceramic package (Case 632).
 Suffix P for TO-116 plastic package (Case 646) MC7404 only.



Positive Logic: $Z = \bar{A}$

Input Loading Factor = 1
 Output Loading Factor = 10
 Total Power Dissipation = 60 mW typ/pkg
 Propagation Delay Time = 13 ns typ


SWITCHING TIME TEST CIRCUIT AND WAVEFORMS



$C_T = 15 \text{ pF}$ = total parasitic capacitance, which includes probe, wiring, and load capacitances.
 The coax delays from input to scope and output to scope must be matched. The scope must be terminated in 50-ohm impedance. The 950-ohm resistor and the scope termination impedance constitute a 20:1 attenuator probe. Coax shall be CT-070-50 or equivalent.

ELECTRICAL CHARACTERISTICS

Test procedures are shown for only one inverter. The other inverters are tested in the same manner.



V = VCC = Pin 14 [4]
Gnd = Pin 7 [11]

Characteristic	Symbol	Pin Under Test	MC5404 Test Limits -55 to +125°C						MC7404 Test Limits 0 to +70°C						TEST CURRENT/VOLTAGE VALUES (All Temperatures)																								
			Min	Max	Unit	Min	Max	Unit	Min	Max	Unit	Volts																											
												mA			I _{OH}	I _{OL}	V _{IL}	V _{IH}	V _{IHH}	V _{R1}	V _{R2}	V _{th1}	V _{th0}	V _{CC}	V _{CCL}	V _{CCH}													
Input Forward Current	I _F	A	-	-1.6	mAdc	-	-1.6	mAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
Leakage Current	I _{R1}	A	-	40	µAdc	-	40	µAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
	I _{R2}	A	-	1.0	mAdc	-	1.0	mAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
	V _{OL}	Z	-	0.4	Vdc	-	0.4	Vdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Output Voltage	V _{OH}	Z	2.4	-	Vdc	2.4	-	Vdc	2.4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Short-Circuit Current	I _{OS} [†]	Z	-20	-55	mAdc	-18	-55	mAdc	-18	-55	mAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Power Requirements (Total Device) Power Supply Drain	I _{PDH}	V	-	33	mAdc	-	33	mAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	I _{PDL}	V	-	12	mAdc	-	12	mAdc	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Switching Parameters	Turn-On Delay	t _{PHL}	A,Z	-	15**	ns	-	15**	ns	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
			A,Z	-	22**	ns	-	22**	ns	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Turn-Off Delay	t _{PLH}	A,Z	-	22**	ns	-	22**	ns	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

* Ground inputs to inverters not under test.
 ** Tested only at 25°C.
 † Only one output should be shorted at a time.



MOTOROLA Semiconductor Products Inc.

BOX 20912 • PHOENIX, ARIZONA 85036 • A SUBSIDIARY OF MOTOROLA INC.

4204-44 PRINTED IN USA 3000, IMPERIAL LITHO 828038 3500

DS 9106