


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	NOTE 1 0.76µm PLATING UPDATE (PdNi+AuFLASH)	11JUL2023	BGC	PS

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH

POS. PER ROW	L±0.4	PART NUMBER		
-	-	-	-	-
2	5.08	828221	-2	OBSOLETE
3	7.62		-3	△2
4	10.16		-4	
5	12.70		-5	OBSOLETE
6	15.24		-6	OBSOLETE
7	17.78		-7	
8	20.32		-8	OBSOLETE △1
9	22.86		-9	OBSOLETE
10	25.40		-0	OBSOLETE
11	27.94		-1	
12	30.48		-2	OBSOLETE
13	33.02		-3	△1
14	35.56		-4	OBSOLETE
15	38.10		-5	△1
16	40.64		-6	△1
17	43.18		-7	OBSOLETE
18	45.72		-8	△1
19	48.26		-9	
20	50.80		-0	
21	53.34		-1	△1
22	55.88		-2	△1
23	58.42		-3	△1
24	60.96		-4	△1
25	63.50		-5	
26	66.04		-6	
27	68.58		-7	
28	71.12		-8	
29	73.66		-9	
30	76.20		-0	
31	78.74		-1	
32	81.28		-2	
33	83.82		-3	
34	86.36		-4	
35	88.90		-5	
36	91.44		-6	
37	93.98		-7	
38	96.52		-8	
39	99.06		-9	
40	101.60		-0	
41	104.14		-1	
42	106.68		-2	
43	109.22		-3	
44	111.76		-4	
45	114.30		-5	
46	116.84		-6	
47	119.38		-7	
48	121.92		-8	
49	124.46		-9	
50	127.00	5- 828221	-0	OBSOLETE △1



- 1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE : MIN. 2.5µm TIN OVER Min 1.27µm NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT PIN	CuZn	△1
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	COLOR FINISH

TE Connectivity. All Rights Reserved. © 2023

DIMENSIONS: mm	DWN	20FEB1985	MATERIAL	SEE TABLE	FINISH	SEE TABLE				
	CHK	22FEB1985	TE TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-								
±0.2 mm	PRODUCT SPEC	108-18012	NAME AMPMODU II PIN HEADER, DUAL ROW							
0 PLC ± -	APPLICATION SPEC	-								
1 PLC ± -	WEIGHT	-	SIZE	A4	CAGE CODE	00779	DRAWING NO	C-828221	RESTRICTED TO	-
2 PLC ± -	CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 1	REV	C1		
3 PLC ± -										
4 PLC ± -										
ANGLES ± -										

