www.elecsuper.com

ElecSuper

SuperESD - ESD05V52D-C-ES

1. Description

The ESD05V52D-C-ES is designed to protect voltage sensitive components from damage or latch-up due to ESD. Excellent clamping capability, low leakage, and fast response time provide best in class protection on designs that are exposed to ESD for board level. Because of its small size and bi-directional design, it is ideal for use in cellular phones, MP3 players, and portable applications that require audio line protection.

2. Features

IEC 61000-4-2 Level 4 ESD Protection

- ±25kV Contact Discharge
- ±25kV Air Discharge
- 80W Peak pulse Power (8/20us)
- Low clamping voltage

- Working voltage: 5V
- Low leakage current
- RoHS compliant
- Protecting one bi-directional lines
- Junction capacitance: 15pF Typ.

3. Applications

- Cellular handsets and accessories
- Portable digital assistants
- Notebooks & handhelds

- Digital cameras
- MP3 players
- Peripherals

4. Ordering Information

Part Number	t Number Package Marking Material Pa		Packing	Quantity	Flammability	Reel	
Fait Number	Гаскаус	Marking	Material	Facking	per reel	Rating	Size
ESD05V52D-C-ES	SOD-523	5XB	Halogen free	Tape & Reel	3,000 PCS	UL 94V-0	7
							inches

Table-1 Ordering information



5. Pin Configuration and Functions

Pin	Name	Description	Outline			Circuit Diagram		
1	IO1	Connect to IO				1		
2	IO2	Connect to IO		5XB	2			
	Table-2 Pin configuration							

6. Specification

6.1. Absolute Maximum rating

Over operating free-air temperature range (unless otherwise noted)

Parameters	Symbol	Min.	Max.	Unit
Peak pulse power (tp=8/20us)@25°C	P _{pk}	-	80	W
Peak pulse current (tp=8/20us)@25°C	I _{PP}		8	А
ESD (IEC61000-4-2 air discharge) @25°C	V_{ESD}	-	±25	kV
ESD (IEC61000-4-2 contact discharge) @25°C	V _{ESD}	-	±25	kV
Junction temperature	TJ	-	150	°C
Operating temperature	T _{OP}	-40	125	°C
Storage temperature	T _{STG}	-55	150	°C
Lead temperature	TL	-	260	°C

Table-3 Absolute Maximum rating




6.2. Electrical Characteristics

At TA = 25°C unl	ess otherwise noted
------------------	---------------------

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Reverse Stand-off Voltage	V _{RWM}				5.0	V
Reverse Breakdown Voltage	V_{BR}	IT=1mA	5.8			V
Reverse Leakage Current	I _R	V _{RWM} =5V			1.0	uA
Clamping Voltage	Vc	I _{PP} =1A; tp=8/20us		7.0	8.0	V
Clamping Voltage	Vc	I _{PP} =8A; tp=8/20us		8.5	10.0	V
Junction Capacitance	CJ	I/O to GND; VR=0V; f=1MHz		15	20	pF

Table-4 Electrical Characteristics

Symbol	Parameters
V _{RWM}	Peak Reverse Working Voltage
I _R	Reverse Leakage Current @ V _{RWM}
V _{BR}	Breakdown Voltage @ I⊤
Ι _τ	Test Current
IPP	Maximum Reverse Peak Pulse Current
Vc	Clamping Voltage @ IPP







Rev-1.2

www.elecsuper.com

7. Typical Characteristic



8. Typical Application




Typical Interface Application



Rev-1.2

www.elecsuper.com

9. Dimension (SOD-523)



Units in millimeters

Unit	A	A1	b	С	D	E	E1	E2	L	θ
Min.	0.58	0.50	0.28	0.08	0.75	1.10	1.50	0.20 REF.	0.01	7° REF.
Max.	0.68	0.70	0.38	0.15	0.85	1.30	1.70		0.07	

ElecSuper

DISCLAIMER

ELECSUPER PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

(1) selecting the appropriate ElecSuper products for your application;

(2) designing, validating and testing your application;

(3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.

