

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C		
	VOLTAGE	50V AC	APPLICABLE CONNECTOR	DF17# (**)-*DS-0. 5V (57)		
	CURRENT	0. 3A				
SPECIFICATIONS						
ITEM	TEST METHOD	REQUIREMENTS	QT	AT		
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X		
MARKING	CONFIRMED VISUALLY.		X	X		
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).	60mΩ MAX.	X	-		
INSULATION RESISTANCE	100V DC.	500MΩ MIN.	X	-		
VOLTAGE PROOF	150V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-		
MECHANICAL CHARACTERISTICS						
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR. 	PIN COUNT	INSERTION FORCE (N)MAX	WITHDRAWAL FORCE (N)MIN	X	-
		30	30.0	3.0		
		40	40.0	4.0		
		50	50.0	5.0		
		60	60.0	6.0		
80	80.0	8.0				
MECHANICAL OPERATION	50TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 60mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35°C TIME 30→10 TO 15→ 30→10TO15min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 250 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	x	-		
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JEIDA-39)	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	x	-		
HEAT RESISTANCE OF SOLDERING	【RECOMMENDED TEMPERATURE PROFILE】 《SOLDERING AREA》 MAX250°C, 220°C FOR 60 SECONDS MAX. 《PREHEATING AREA》 150 TO 180°C 120 SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. 【RECOMMENDED MANUAL SOLDELING CONDITION】 SOLDERING IRON TEMPERATURE 350°C SOLDERING TIME : WITHIN 3 SECONDS.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	-		
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	1	DIS-H-00003088	SH. HOSODA	TS. MIYAZAKI	17. 09. 29	
REMARKS NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT. UNLESS OTHERWISE SPECIFIED,REFER TO JIS C 0806.			APPROVED	MO. NAKAMURA	05. 05. 20	
			CHECKED	TS. MIYAZAKI	05. 05. 19	
			DESIGNED	YH. MICHIDA	05. 05. 19	
			DRAWN	YH. MICHIDA	05. 05. 19	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-162140-06		
	SPECIFICATION SHEET		PART NO.	DF17A (4. 0)-*DP-0. 5V (57)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL683	 1/1	