


REVISIONS			
REV	DESCRIPTION	DATE	APPV
Α	PRODUCTION RELEASE	JHAGER 5/31/22	DV 5/31/22

## NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
- DIMENSIONS APPLY AFTER FINISHING.
- MANUFACTURE TO BE COMPLIANT WITH EU ROHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. ELECTRICAL SPECIFICATIONS ARE FOR LISTED FOR REFERENCE ONLY. SEE LINX DATA SHEET FOR CURRENT PROPERTIES
  - 1. CONTACT RESISTANCE: NTE  $30m\Omega$
  - 2. INSULATION RESISTANCE:  $1G\Omega$  MAX
  - 3. DIELECTRIC RESISTANCE: 500VAC
- 5. MECHANICAL PROPERTIES
  - 1. MATERIAL: LPC, WHITE, UL94V-0
  - 2. OPERATING TEMPERATURE: -25º +85ºC
  - 3. UNLISTED DIMENSIONS CONTROLLED BY SOLID MODEL AT LATEST REVISION.
- 6. PACKAGE IN TAPE AND REEL IAW ASTM EIA-481-F
  - 1. PITCH: 20mm
  - 2. TAPE SIZE: 44mm
  - 3. EMBOSSED CARRIER
- 7. LABEL PACKAGING (TRAY, LOT-BAGS AND BOXES) AS SHOWN ON LINX DRAWING [MEC-LBL-4X2.5-PAPER-ID]



DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS **DESIGNATED AGENTS.** MATERIAL INTERPRET DIMENSIONS AND **TOLERANCES PER ASME Y14.5.** PROJECTION: LCP  $.X \pm 2.0$ ANGLES: ±1 .XX +1.00 CuSnP SURFACE:  $\sqrt[32]{}$ .XXX ±.500 FINISH: DT: 5/31/22 DRAWN: JHAGER WHITE **ENGR: SHAWNH** DT: 5/31/22 Sn 100u"

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION

THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE

TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS



159 ORT LANE MERLIN, OR 97532

TITLE:

BATTERY HOLDER SURFACE MNT SOLDER CR2032

SIZE DWG. NO. REV

C-BAT-HLD-013-SMT-TR

SCALE: 2:1 DO NOT SCALE DRAWING SHEET 1 OF 1