

Jan.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	VOLTAGE	△ 60 V AC/DC		STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX	
	CURRENT	2 A			(NOT DEWED)	
SPECIFICATIONS						
ITEM	TEST METHOD			REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.				x	x
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE	1A DC.			10 mΩ MAX .	-	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	10 mV AC MAX, 0.1 mA(DC OR 1000Hz)			10 mΩ MAX .	-	-
INSULATION RESISTANCE	500 V DC.			100 MΩ MIN.	x	-
VOLTAGE PROOF	1000 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.	-	-
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 20 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
SHOCK	981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.			① 100 N MIN	x	-
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 20 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.			① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
DRY HEAT	EXPOSED AT 140°C, 120 h.			① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
COLD	EXPOSED AT -40°C , 120 h.			① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RESISTANCE TO SO ₂ GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.			① CONTACT RESISTANCE: 20 mΩ MAX.	-	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	1	DIS-T-00006021	YH. MAMADA	HH. TSUKUMO	20200403	
REMARK				APPROVED	HK. UMEHARA	20171016
(NOTE1) "STORAGE" means a long-term storage state for the unused product before assembly to PCB.				CHECKED	HK. UMEHARA	20171016
				DESIGNED	TY. ISHIGURO	20171016
				DRAWN	MN. SATOH	20171013
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-368640-00-00		
HRS	SPECIFICATION SHEET		PART NO.	ZE05-16DS-HU/R		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL752-2205-0-00	△	1/1