

Jan.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	VOLTAGE	300 V AC	OPERATING HUMIDITY RANGE	85%MAX (NON-CONDENSING)	
	CURRENT	2 A	STORAGE HUMIDITY RANGE		
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).		20 mΩ MAX.	X	—
INSULATION RESISTANCE	100 V DC.		10 ⁶ MΩ MIN.	X	—
VOLTAGE PROOF	1000 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s ² FOR 2 h, IN 3 DIRECTIONS.		1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms FOR 3 TIME IN 3 DIRECTION.			X	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) INSULATION RESISTANCE:	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -65→15 TO 35→+125→15 TO 35°C TIME 30→ MAX5 → 30 →MAX5min. UNDER 5 CYCLES.		10 ⁶ MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO HEAVY CORROSION.	X	—
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
REMARK			APPROVED	HS. OKAWA	12.06.11
			CHECKED	HT. YAMAGUCHI	12.06.11
			DESIGNED	KJ. NISHIWAKI	12.06.11
			DRAWN	GR. TAKEISHIMA	12.06.11
Unless otherwise specified, refer to MIL-STD-1344.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-019798-01
	SPECIFICATION SHEET		PART NO.	PCN12A-44P-2. 54DS (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL583-2014-4-71	1/1