

## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-1YC38-0UB0

Client order no. : Order no. : Offer no. : Remarks :

Rated data				
Input				
	Number of phases	3 AC		
	Line voltage	200 240 V +10 %	-20 %	
	Line frequency	47 63 Hz		
	Rated voltage	200V IEC	240V NEC	
	Rated current (LO)	149.00 A	149.00 A	
	Rated current (HO)	126.00 A	126.00 A	
Output				
	Number of phases	3 AC		
	Rated voltage	200V IEC	240V NEC 1)	
	Rated power (LO)	45.00 kW	60.00 hp	
	Rated power (HO)	37.00 kW	50.00 hp	
	Rated current (LO)	154.00 A	154.00 A	
	Rated current (HO)	130.00 A	130.00 A	
	Rated current (IN)	158.00 A		
	Max. output current	208.00 A		
Pulse frequency		4 kHz		
Output frequency for vector control		0 200 Hz		
Output frequency for V/f control		0 550 Hz		
Overload capability				
	ow Overload (LO)			

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

 $150\%\,x$  base load current IH for 60 s within a 600 s cycle time

General tech. specifications			
Power factor λ	0.90 0.95		
Offset factor $\cos\phi$	0.99		
Efficiency η	0.97		
Sound pressure level (1m)	72 dB		
Power loss 3)	1.810 kW		
Filter class (integrated)	Unfiltered		
EMC category (with accessories)	without		
Safety function "Safe Torque Off"	without		
Communication			

Communication

USS, Modbus RTU, BACnet MS/TP



Item no. : Consignment no. : Project :

Inputs / outputs				
Standard digital inputs				
Number	6			
Switching level: $0 \rightarrow 1$	11 V			
Switching level: $1 \rightarrow 0$	5 V			
Max. inrush current	15 mA			
Fail-safe digital inputs				
Number	1			
Digital outputs				
Number as relay changeover contact	2			
Output (resistive load)	DC 30 V, 5.0 A			
Number as transistor	0			
Analog / digital inputs				
Number	2 (Differential input)			
Resolution	10 bit			
Switching threshold as digital input				
0 → 1	4 V			
1 → 0	1.6 V			
Analog outputs				
Number	1 (Non-isolated output)			

## PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy  $\pm 5~^\circ\text{C}$ 

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	




## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-1YC38-0UB0

Class 3C3, according to IEC 60721-3-3: 2002				
Air cooling using an integrated for				
Air cooling using an integrated fan				
0.153 m³/s (5.403 ft³/s)				
1,000 m (3,280.84 ft)				
Ambient temperature				
-20 45 °C (-4 113 °F)				
-40 70 °C (-40 158 °F)				
-25 55 °C (-13 131 °F)				
Relative humidity				
95 % At 40 °C (104 °F), condensation and icing not permissible				
ections				
Signal cable				
0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)				
M10 screw				
35.00 2 x 120.00 mm <sup>2</sup> (AWG 1 AWG 2 x 4/0)				
M10 screw				
35.00 2 x 120.00 mm <sup>2</sup> (AWG 1 AWG 2 x 4/0)				
DC link (for braking resistor)				
M10 screw				
Max. motor cable length				
300 m (984.25 ft)				

Mechanical data				
Degree of protection	IP20 / UL open type			
Frame size	FSF			
Net weight	17.6 kg (38.80 lb)			
Dimensions				
Width	305 mm (12.01 in)			
Height	709 mm (27.91 in)			
Depth	369 mm (14.53 in)			
Standards				
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH			
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC			





The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 220V-240V

<sup>&</sup>lt;sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.