

■ PRODUCT CHARACTERISTICS


|                                |       |
|--------------------------------|-------|
| VDSS                           | 500V  |
| $R_{DS(on)Typ}(@V_{GS} = 10V)$ | 0.36Ω |
| Qg@type                        | 33 nC |
| ID                             | 15A   |

■ APPLICATIONS

- \* High efficiency switch mode power supplies
- \* Electronic lamp ballasts based on half bridge
- \* LED power supplies

■ FEATURES

- \* Fast switching capability
- \* Avalanche energy specified
- \* Improved dv/dt capability, high ruggedness



■ ORDER INFORMATION

| Order codes  |           | Package | Packing        |
|--------------|-----------|---------|----------------|
| Halogen-Free | Halogen   |         |                |
| N/A          | MOT15N50F | TO-220F | 50 pieces/Tube |
| N/A          | MOT15N50A | TO-220  | 50 pieces/Tube |

■ ABSOLUTE MAXIMUM RATINGS ( $T_C = 25^\circ C$ , unless otherwise specified)

| Parameter                          | Symbol                 | Ratings    | Unit |
|------------------------------------|------------------------|------------|------|
| Drain to Source Voltage            | $V_{DSS}$              | 500        | V    |
| Gate to Source Voltage             | $V_{GSS}$              | ±30        | V    |
| Avalanche Current (Note 2)         | $I_{AR}$               | 15         | A    |
| Continuous Drain Current           | Continuous             | $I_D$      | 15   |
|                                    | Pulsed (Note 2)        | $I_{DM}$   | 60   |
| Avalanche Energy                   | Single Pulsed (Note 3) | $E_{AS}$   | 637  |
|                                    | Repetitive (Note 2)    | $E_{AR}$   | 25   |
| Peak Diode Recovery dv/dt (Note 4) | dv/dt                  | 4.5        | V/ns |
| Power Dissipation                  | TO-220F                | $P_D$      | 38.5 |
|                                    | TO-220AB               |            | 300  |
| Junction Temperature               | $T_J$                  | +150       | °C   |
| Storage Temperature                | $T_{STG}$              | -55 ~ +150 | °C   |

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by maximum junction temperature

3.  $L=5.23mH$ ,  $I_{AS}=15A$ ,  $V_{DD}=50V$ ,  $R_G=25\Omega$ , Starting  $T_J=25^\circ C$

4.  $I_{SD} \leq 15A$ ,  $di/dt \leq 200A/\mu s$ ,  $V_{DD} \leq BV_{DSS}$ , Starting  $T_J=25^\circ C$

■ ELECTRICAL CHARACTERISTICS ( $T_C=25^\circ\text{C}$ , unless otherwise noted)

| Parameter                                       | Symbol                       | Test conditions   | Min | Typ  | Max       | Units                     |
|---|------------------------------|---|-----|------|-----------|---------------------------|
| Static  |                              |   |     |      |           |                           |
| Drain to Source Breakdown Voltage               | $B_{VDSS}$                   | $I_D = 250\mu\text{A}$ , $V_{GS} = 0\text{V}$   | 500 | -    | -         | V                         |
| Breakdown Voltage Temp. Coefficient             | $\Delta B_{VDSS}/\Delta T_J$ | Reference to $25^\circ\text{C}$ ,<br>$I_D = 1\text{mA}$                                     | -   | 0.58 | -         | $\text{V}/^\circ\text{C}$ |
| Drain to Source On-Resistance                   | $r_{DS(ON)}$                 | $V_{GS} = 10\text{V}$ , $I_D = 7.5\text{A}$   | -   | 0.36 | 0.40      | $\Omega$                  |
| Gate Threshold Voltage                          | $V_{GS(th)}$                 | $V_{DS} = V_{GS}$ , $I_D = 250\mu\text{A}$  | 2.0 | 3.4  | 4.0       | V                         |
| Zero Gate Voltage Drain Current                 | $I_{DSS}$                    | $V_{DS} = 500\text{V}$ ,<br>$V_{GS} = 0\text{V}$  | -   | -    | 1         | $\mu\text{A}$             |
|   |                              |   | -   | -    | 250       | $\mu\text{A}$             |
| Gate to Source Leakage Current                  | $I_{GSS}$                    | $V_{GS} = \pm 30\text{V}$   | -   | -    | $\pm 100$ | nA                        |
| Dynamics  |                              |   |     |      |           |                           |
| Forward Transconductance                        | $g_{fs}$                     | $V_{DD} = 10\text{V}$ , $I_D = 7.5\text{A}$   | 10  | -    | -         | S                         |
| Total Gate Charge at 10V                        | $Q_{g(TOT)}$                 | $V_{GS} = 10\text{V}$ ,<br>$V_{DS} = 400\text{V}$ ,<br>$I_D = 15\text{A}$                   | -   | 33   | 41        | nC                        |
| Gate to Source Gate Charge                      | $Q_{gs}$                     |   | -   | 7.2  | 10        | nC                        |
| Gate to Drain "Miller" Charge                   | $Q_{gd}$                     |   | -   | 12   | 16        | nC                        |
| Turn-On Delay Time                              | $t_{d(ON)}$                  |   | -   | 9    | -         | ns                        |
| Rise Time                                       | $t_r$                        | $V_{DD} = 250\text{V}$ ,<br>$I_D = 15\text{A}$ ,<br>$R_G = 6.2\Omega$ ,<br>$R_D = 17\Omega$ | -   | 5.4  | -         | ns                        |
| Turn-Off Delay Time                             | $t_{d(OFF)}$                 |   | -   | 26   | -         | ns                        |
| Fall Time                                       | $t_f$                        |   | -   | 5    | -         | ns                        |
| Input Capacitance                               | $C_{ISS}$                    | $V_{DS} = 25\text{V}$ , $V_{GS} = 0\text{V}$ ,<br>$f = 1\text{MHz}$                         | -   | 1850 | -         | pF                        |
| Output Capacitance                              | $C_{OSS}$                    |   | -   | 230  | -         | pF                        |
| Reverse Transfer Capacitance                    | $C_{RSS}$                    |   | -   | 16   | -         | pF                        |
| Avalanche characteristics                       |                              |   |     |      |           |                           |
| Single Pulse Avalanche Energy <sup>2</sup>      | $E_{AS}$                     |   | 760 | -    | -         | mJ                        |
| Avalanche Current                               | $I_{AR}$                     |   | -   | -    | 15        | A                         |
| Drain-source diode characteristics              |                              |   |     |      |           |                           |
| Continuous Source Current (Body Diode)          | $I_S$                        |   | -   | -    | 15        | A                         |
| Pulsed Source Current <sup>1</sup> (Body Diode) | $I_{SM}$                     |   | -   | -    | 60        | A                         |
| Source to Drain Diode Voltage                   | $V_{SD}$                     | $I_{SD} = 15\text{A}$   | -   | 0.86 | 1.2       | V                         |
| Reverse Recovery Time                           | $t_{rr}$                     | $I_{SD} = 15\text{A}$ , $di_{SD}/dt = 100\text{A}/\mu\text{s}$                              | -   | 470  | 730       | ns                        |
| Reverse Recovered Charge                        | $Q_{RR}$                     | $I_{SD} = 15\text{A}$ , $di_{SD}/dt = 100\text{A}/\mu\text{s}$                              | -   | 5    | 6.6       | $\mu\text{C}$             |

Notes:

- 1: Repetitive rating; pulse width limited by maximum junction temperature  
2: Starting  $T_J = 25^\circ\text{C}$ ,  $L = 7.0\text{mH}$ ,  $I_{AS} = 15\text{A}$

■ TEST CIRCUITS AND WAVEFORMS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Transfer Characteristics




Figure 4. Normalized Drain To Source On Resistance vs Junction Temperature




Figure 5. Capacitance vs Drain To Source Voltage




Figure 6. Gate Charge Waveforms For Constant Gate Current

■ TYPICAL CHARACTERISTICS




Figure 7. Body Diode Forward Voltage vs Body Diode Current




Figure 8. Maximum Safe Operating Area




Figure 9. Maximum Drain Current vs Case Temperature





Figure 10. Unclamped Inductive Switching Capability





■ TO-220 PACKAGE OUTLINE DIMENSIONS

