

# RLP73N1JR13JTD ✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 1-2176052-1

.13  $\Omega$ , Thick Film, Low Ohmic Resistor, 5 %, 2 Termination, 0603, Taped & Reeled, .125 W,  $\pm 300$  ppm/ $^{\circ}\text{C}$ , Solder, Height .018 in [.45 mm], CGS RLP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Low Ohmic Resistor**

Number of Terminations: **2**

Package Size Code: **0603**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

[All Thick Film Resistor: Current Sense \(214\)](#)

## Features

### Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Low Ohmic Resistor |
| Package Size Code | 0603               |
| Element Type      | Thick Film         |

### Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

### Electrical Characteristics

|                             |                   |
|-----------------------------|-------------------|
| Passive Component Tolerance | 5 %               |
| Resistance Class            | Up to 1k $\Omega$ |
| Resistance Value            | .13 $\Omega$      |
| Power Rating                | .125 W            |

### Termination Features

|   |        |
|---|--------|
| Number of Terminations                  | 2      |
| Surface Mount Resistor Termination Type | Solder |

### Dimensions

|                |                 |
|----------------|-----------------|
| Product Height | .45 mm[.018 in] |
| Product Length | 1.6 mm[.063 in] |



|               |                |
|---------------|----------------|
| Product Width | .8 mm[.031 in] |
|---------------|----------------|

**Usage Conditions**

|                         |             |
|-------------------------|-------------|
| Temperature Coefficient | ±300 ppm/°C |
|-------------------------|-------------|

**Packaging Features**

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions   |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not reviewed for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**




TE Part # CAT-C339-R529A  
Thick Film Resistor: Current Sense



TE Part # 2176050-8  
RLP73N 1E R10 5% 5K RL

### Also in the Series | CGS RLP73



Surface Mount Resistors(401)

### Customers Also Bought



TE Part #8-1879233-4  
SMW5 300R 5%



TE Part #6-104935-0  
10 MTE HDR SRRA LTCH.100CL LF



TE Part #5-103635-6  
07 MTE HDR SRRA LTCH.100CL LF



TE Part #292230-4  
1.5 MINI CT SGL V SMT W/BOSS 4



TE Part #1-1825059-2  
ADF03STTR04=DIP S,FLUSH,SMT-GW



TE Part #1879217-2  
CPF 0603 150K 0.1% 25PPM 1K RL



TE Part #4-1676481-2  
CPF 0603 300R 0.1% 25PPM 1K RL



TE Part #6-104363-0  
11 MTE HDR SRST LATCH .100CL



TE Part #7-1623932-2  
CFR50 5% 2K2



TE Part #6-104935-1  
11 MTE HDR SRRA LTCH.100CL LF



## Documents

### Product Drawings

[RLP73N 1J R13 5% 5K RL](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176052-1\\_BA.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176052-1\\_BA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176052-1\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[SMD Low Ohmic Current Sense Resistors - Type RL73 Series](#)

English