



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0805**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	.1 %
Resistance Class	1k $\Omega$ – 1M $\Omega$
Resistance Value	1M $\Omega$
Power Rating	.1 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]

Usage Conditions



Temperature Coefficient	$\pm 25$ ppm/ $^{\circ}\text{C}$
-------------------------	----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-2176215-5 CPF A 0402 68K 0.1% 25PPM 1K RL	 TE Part # 6-2176216-5 CPF A 0603 200K 0.1% 25PPM 1K RL	 TE Part # 4-2176217-9 CPF A 0805 10K 0.1% 25PPM 1K RL	 TE Part # 5-2176217-6 CPF A 0805 25K 0.1% 25PPM 1K RL
--	---	--	--

CPF-A-0805B1M0E1

1M  $\Omega$ , Thin Film, Precision Resistor, .1 %, 2 Termination, 0805, Taped & Reeled, .1 W,  $\pm 25$  ppm/ $^{\circ}\text{C}$ , Solder, Height .022 in [.55 mm], Neohm CPF



TE Part # 2-2176237-5  
CPF A 0603 680R 0.1% 25PPM 5K RL

Also in the Series | Neohm CPF

Surface Mount Resistors(6124)

Customers Also Bought

TE Part #2-1761713-3  
IDC LOW PRO HDR 10P VERT SHT L

TE Part #5767096-1  
MICT,REC,038,ASY,.025,TAPE PKG

TE Part #1-1393238-9  
RTB14024

TE Part #5-1625890-2  
2W SM M/OX 5% 47K

TE Part #2-1393238-6  
RTB14730

TE Part #1623118-1  
CRG0805 1% 15K

TE Part #6-2176328-1  
CRGP 1206 1M0 1%

TE Part #2176329-1  
CRGP 1210 10R 1%

TE Part #1-1676480-3  
CRG0402 1% 150K



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_7-2176217-0\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_7-2176217-0\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_7-2176217-0\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Grade Thin Film Chip Resistor - Type CPF-A Series

English