

#### **Description**

The ZXMN3B01F uses advanced trench technology to provide excellent  $R_{\text{DS}(\text{ON})}$ , low gate charge and operation with gate voltages as low as 2.5V. This

device is suitable for use as a

# Battery protection or in other Switching application.

#### **General Features**

 $V_{DS} = 30V I_{D} = 5A$ 


 $R_{DS(ON)}$  < 42m $\Omega$  @  $V_{GS}$ =10V

## **Application**

Battery protection

Load switch

Uninterruptible power supply



N-Channel MOSFET

#### **Package Marking and Ordering Information**

Product ID	Pack	Brand	Qty(PCS)
ZXMN3B01F	SOT-23	HXY MOSFET	3000

## Absolute Maximum Ratings (T<sub>A</sub>=25 ℃ unless otherwise noted)

Symbol	Parameter	Limit	Unit	
V <sub>DS</sub>	Drain-Source Voltage	30	V	
V <sub>G</sub> S	Gate-Source Voltage	±12	V	
I <sub>D</sub>	I <sub>D</sub> Drain Current-Continuous			
Ідм	Drain Current-Pulsed (Note 1)	14.4	А	
P <sub>D</sub>	P <sub>D</sub> Maximum Power Dissipation		W	
T <sub>J</sub> ,T <sub>STG</sub>	T <sub>J</sub> ,T <sub>STG</sub> Operating Junction and Storage Temperature Range		°C	
RөJA	Thermal Resistance,Junction-to-Ambient (Note 2)	125	°C/W	



### Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250uA	30			V	
Dagger	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =10V , I <sub>D</sub> =3A		33	42	mΩ	
R <sub>DS(ON)</sub>		V <sub>GS</sub> =4.5V , I <sub>D</sub> =2A		38	48		
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250uA	0.4		1.2	V	
	Drain-Source Leakage Current	V <sub>DS</sub> =16V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C			1		
IDSS		V <sub>DS</sub> =16V , V <sub>GS</sub> =0V , T <sub>J</sub> =55°C			5	uA	
Igss	Gate-Source Leakage Current	V <sub>GS</sub> =±12V , V <sub>DS</sub> =0V			±100	nA	
gfs	Forward Transconductance	V <sub>DS</sub> =5V , I <sub>D</sub> =3A		10.5		S	
Qg	Total Gate Charge (4.5V)			4.6			
Qgs	Gate-Source Charge	V <sub>DS</sub> =15V , V <sub>GS</sub> =4.5V , I <sub>D</sub> =3A		0.7		nC	
Q <sub>gd</sub>	Gate-Drain Charge			1.5			
T <sub>d(on)</sub>	Turn-On Delay Time			1.6			
Tr	Rise Time $V_{DD}$ =10V , $V_{GS}$ =4.5V , $R_{G}$ =3.3 $\Omega$			42			
T <sub>d(off)</sub>	Turn-Off Delay Time	I <sub>D</sub> =3A		14		ns	
T <sub>f</sub>	Fall Time			7			
C <sub>iss</sub>	Input Capacitance			310			
Coss	Output Capacitance	V <sub>DS</sub> =15V , V <sub>GS</sub> =0V , f=1MHz		49		pF	
Crss	Reverse Transfer Capacitance			35			

#### **Diode Characteristics**


Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current <sup>1,4</sup>	V <sub>G</sub> =V <sub>D</sub> =0V , Force Current	-		3.6	Α
V <sub>SD</sub>	Diode Forward Voltage <sup>2</sup>	V <sub>GS</sub> =0V , I <sub>S</sub> =1A , T <sub>J</sub> =25°C			1.2	V

#### Note:

- 1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width  $\,\leq\,300\text{us}$  , duty cycle  $\,\leq\,2\%$
- 3.The power dissipation is limited by 150°C junction temperature
- 4. The data is theoretically the same as  $I_D$  and  $I_{DM}$ , in real applications, should be limited by total power dissipation.



#### **Typical Characteristics**



**Fig.1 Typical Output Characteristics** 




Fig.3 Forward Characteristics of Reverse




Fig.5 Normalized V<sub>GS(th)</sub> vs. T<sub>J</sub>




Fig.2 On-Resistance vs. Gate-Source Voltage




Fig.4 Gate-Charge Characteristics





Fig.6 Normalized R<sub>DSON</sub> vs. T<sub>J</sub>








Fig.7 Capacitance

Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform







Fig.11 Gate Charge Waveform



## **SOT-23 Package Outline Dimensions**








Symbol	Dimensions In Millimeters		Dimensions In Inches		
Symbol	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022 REF		
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

## **SOT-23 Suggested Pad Layout**



#### Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:± 0.05mm.
  3.The pad layout is for reference purposes only.



#### **Attention**

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.