


- 注記  
NOTES
- 材質：りん青銅, t=0.152  
MATERIAL: PHOSPHOR BRONZE, t=0.152
  - メッキ仕様  
PLATING  
接点部:  
CONTACT AREA:  
金メッキ: 0.1 μm MIN.  
GOLD: 0.1 MICROMETER MIN.  
ニッケルメッキ: 1.5 μm MIN. (下地メッキ)  
NICKEL: 1.5 μm MIN. (UNDER PLATING)  
圧着部:  
CRIMP AREA:  
錫メッキ: 1.0 μm MIN.  
TIN: 1.0 MICROMETER MIN.
  - 適合ハウジングアッセンブリ: 55833-\*\*\*\*  
APPLICABLE HOUSING ASS'Y: 55833-\*\*\*\*
  - ELV 及び RoHS 適合品  
ELV AND RoHS COMPLIANT.



バラ状 LOOSE	56160-8131
連鎖状 CHAIN	56160-8031
端子形状 FORM	MATERIAL NO.

RELEASED EC NO: J2008-4369 DRWN: NABEI 2008/06/26 CHKD: KTOYODA 2008/06/26 APPR: NUKITA 2008/06/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
	10 UNDER	±0.2	DRAWN BY M. NABEI	DATE '08/06/23	TITLE SMEC (SERVO MOTOR ENCODER CONN.) CRIMP PIN			
	10 OVER 30 UNDER	±0.25	CHECKED BY K. TOYODA	DATE '08/06/23				
	30 OVER	±0.3	APPROVED BY N. UKITA	DATE '08/06/23	MOLEX INCORPORATED			
	ANGULAR	±3 °	MATERIAL NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-56160-003		1 OF 1		