

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C			
	VOLTAGE	50V AC	APPLICABLE CONNECTOR	DF17# (3.0H) -*DS-0.5V (57)			
	CURRENT	0.3A					
SPECIFICATIONS							
ITEM	TEST METHOD		REQUIREMENTS	QT	AT		
CONSTRUCTION							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X		
MARKING	CONFIRMED VISUALLY.			X	X		
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).		60mΩ MAX.	X	-		
INSULATION RESISTANCE	100V DC.		500MΩ MIN.	X	-		
VOLTAGE PROOF	150V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	-		
MECHANICAL CHARACTERISTICS							
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR. 		PIN COUNT	INSERTION FORCE (N)MAX	WITHDRAWAL FORCE (N)MIN	X	-
			26	26.6	2.6		
			30	30.0	3.0		
			60	60.0	6.0		
			70	70.0	7.0		
			80	80.0	8.0		
MECHANICAL OPERATION	50TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 60mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
ENVIRONMENTAL CHARACTERISTICS							
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35°C TIME 30→10 TO 15→ 30→10TO15min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 250 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-		
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	x	-		
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JEIDA-39)		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	x	-		
HEAT RESISTANCE OF SOLDERING	【RECOMMENDED TEMPERATURE PROFILE】 《SOLDERING AREA》 MAX250°C, 220°C FOR 60 SECONDS MAX. 《PREHEATING AREA》 150 TO 180°C 120 SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. 【RECOMMENDED MANUAL SOLDELING CONDITION】 SOLDERING IRON TEMPERATURE 350°C SOLDERING TIME : WITHIN 3 SECONDS.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	-		
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
	1	DIS-H-00003088	SH. HOSODA	TS. MIYAZAKI	17. 09. 29		
REMARKS			APPROVED	MO. NAKAMURA	05. 04. 20		
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT.			CHECKED	TS. MIYAZAKI	05. 04. 19		
UNLESS OTHERWISE SPECIFIED,REFER TO JIS C 0806.			DESIGNED	YH. MICHIDA	05. 04. 19		
			DRAWN	YH. MICHIDA	05. 04. 19		
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-162765-06			
	SPECIFICATION SHEET		PART NO.	DF17 (1.0H) -*DP-0.5V (57)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL683	 1/1		