


## **Data sheet for SINAMICS G120X**

6SL3230-1YH44-0CF0 Article No.:

Client order no. : Order no.: Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

Communication

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	72 dB	
Power loss 3)	1.820 kW	
Filter class (integrated)	RFI suppression filter for Category C3	
EMC category (with accessories)	Category C3	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

PROFINET, EtherNet/IP



Item no.: Consignment no. : Project :

· · · · · · · · · · · · · · · · · · ·	outputs		
Standard digital inputs			
Number	6		
Switching level: $0 \rightarrow 1$	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
0 → 1	4 V		
1 → 0	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		

## PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-1YH44-0CF0

Ambient conditions			
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.153 m³/s (5.403 ft³/s)		
Installation altitude	1,000 m (3,280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		
Relative humidity			
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible		
Connections			
Signal cable			
Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)		
Line side			
Version	M10 screw		
Conductor cross-section	35.00 2 x 120.00 mm <sup>2</sup> (AWG 1 AWG 2 x 4/0)		
Motor end			
Version	M10 screw		
Conductor cross-section	35.00 2 x 120.00 mm <sup>2</sup> (AWG 1 AWG 2 x 4/0)		
DC link (for braking resistor)			
PE connection	M10 screw		
Max. motor cable length			
Max. motor cable length  Shielded	150 m (492.13 ft)		

Mechanical data				
Degree of protection		IP20 / UL open type		
Frame size		FSF		
Net weight		68 kg (149.91 lb)		
Dimensions				
	Width	305 mm (12.01 in)		
	Height	709 mm (27.91 in)		
	Depth	369 mm (14.53 in)		
Standards				
Compliance with standards		UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		

Converter losses to IEC61800-9-2*		
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	37.0 %	



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 550V-600V

<sup>&</sup>lt;sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.