

Description

The IRFU4105ZPBF uses advanced trench technology to provide excellent R_{DS(ON)}, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.



TO-252-2L

General Features

 $V_{DS} = 60V I_{D} = 50 A$


 $R_{DS(ON)}$ < 17m Ω @ V_{GS} =10V

Application

Battery protection

Load switch

Uninterruptible power supply



N-Channel MOSFET

Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
IRFU4105ZPBF	TO-252-2L	HXY MOSFET	2500

Absolute Maximum Ratings (T_C=25°Cunless otherwise noted)

Symbol	Parameter Rating		Units	
Vps	Drain-Source Voltage	60	V	
Vgs	Gate-Source Voltage	Gate-Source Voltage ±20		
I _D @T _C =25°C	Continuous Drain Current, V _{GS} @ 10V ¹	uous Drain Current, V _{GS} @ 10V ¹ 50		
I _D @T _C =100°C	Continuous Drain Current, V _{GS} @ 10V ¹	nuous Drain Current, V _{GS} @ 10V ¹ 38		
Ірм	Pulsed Drain Current ²	Pulsed Drain Current ² 180		
EAS	Single Pulse Avalanche Energy ³	Single Pulse Avalanche Energy ³ 280		
las	Avalanche Current	28	А	
P _D @T _C =25°C	Total Power Dissipation ⁴	Total Power Dissipation ⁴ 87.7		
Тѕтс	Storage Temperature Range	Storage Temperature Range -55 to 150		
TJ	Operating Junction Temperature Range	on Temperature Range -55 to 150		
R _θ JA	Thermal Resistance Junction-Ambient ¹	62	°C/W	



Electrical Characteristics (T_C=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Off Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	60	-	-	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =60V,V _{GS} =0V	-	-	1	μΑ
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V	-	-	±100	nA
On Characteristics (Note 3)						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_{D}=250\mu A$	1.0	1.5	2.5	V
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =30A	-	13	17	mΩ
Forward Transconductance	g FS	V _{DS} =5V,I _D =30A	30	-	-	S
Dynamic Characteristics (Note4)	1		•			
Input Capacitance	C _{lss}		-	2498	-	PF
Output Capacitance	Coss	$V_{DS}=25V,V_{GS}=0V,$	-	185	-	PF
Reverse Transfer Capacitance	C _{rss}	F=1.0MHz	-	80	-	PF
Switching Characteristics (Note 4)	1		•			•
Turn-on Delay Time	t _{d(on)}		-	12	-	nS
Turn-on Rise Time	t _r	V_{DD} =30V, I_D =2A, R_L =1 Ω	-	5.2	-	nS
Turn-Off Delay Time	$t_{d(off)}$	V_{GS} =10V, R_{GEN} =3 Ω	-	38	-	nS
Turn-Off Fall Time	t _f		-	27	-	nS
Total Gate Charge	Q_g	V 20V/1 20A	-	36	-	nC
Gate-Source Charge	Q_{gs}	V_{DS} =30V, I_{D} =30A, V_{GS} =10V	-	9.9	-	nC
Gate-Drain Charge	Q_{gd}	V _{GS} -10V	-	6.6	-	nC
Drain-Source Diode Characteristics	1		•			•
Diode Forward Voltage (Note 3)	V _{SD}	V _{GS} =0V,I _S =30A	-	-	1.2	V
Diode Forward Current (Note 2)	Is		-	-	58	Α
Reverse Recovery Time	t _{rr}	TJ = 25°C, IF =30A	-	35		nS
Reverse Recovery Charge	Qrr	di/dt = 100A/µs ^(Note3)	-	47		nC
Forward Turn-On Time	t _{on}	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)				

Notes:

- **1.** Repetitive Rating: Pulse width limited by maximum junction temperature.
- 2. Surface Mounted on FR4 Board, t ≤ 10 sec.
- 3. Pulse Test: Pulse Width ≤ 300µs, Duty Cycle ≤ 2%.
- 4. Guaranteed by design, not subject to production
- **5.** E_{AS} condition: $Tj=25\,^{\circ}\mathrm{C}$, $V_{DD}=30V$, $V_{G}=10V$,L=0.5mH, $Rg=25\Omega$

Typical Electrical and Thermal Characteristics (Curves)




Figure 1 Output Characteristics




Figure 4 Rdson-JunctionTemperature




Figure 2 Transfer Characteristics




Figure 5 Gate Charge




Figure 3 Rdson- Drain Current





Figure 6 Source- Drain Diode Forward







Figure 7 Capacitance vs Vds

Figure 9 Power De-rating








Figure 8 Safe Operation Area

Figure 10 ID Current- JunctionTemperature



60

TO-252-2L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches			
	Min.	Max.	Min.	Max.		
А	2.200	2.400	0.087	0.094		
A1	0.000	0.127	0.000	0.005		
b	0.660	0.860	0.026	0.034		
С	0.460	0.580	0.018	0.023		
D	6.500	6.700	0.256	0.264		
D1	5.100	5.460	0.201	0.215		
D2	0.483 TYP.		0.190 TYP.			
E	6.000	6.200	0.236	0.244		
е	2.186	2.386	0.086	0.094		
L	9.800	10.400	0.386	0.409		
L1	2.900 TYP.		0.114 TYP.			
L2	1.400	1.700	0.055	0.067		
L3	1.600	1.600 TYP.		0.063 TYP.		
L4	0.600	1.000	0.024	0.039		
Ф	1.100	1.300	0.043	0.051		
θ	0°	8°	0°	8°		
h	0.000	0.300	0.000	0.012		
V	5.350 TYP.		0.211 TYP.			



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc.

 When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.