

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
<b>APPLICATION STANDARD</b>									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C							
	VOLTAGE	100 V AC							
	CURRENT	0.4 A							
<b>SPECIFICATIONS</b>									
ITEM		TEST METHOD			REQUIREMENT			QT	AT
<b>CONSTRUCTION</b>									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING			X	X
MARKING		CONFIRMED VISUALLY						X	X
<b>ELECTRICAL CHARACTERISTICS</b>									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz)			45 mΩ MAX.			X	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA (DC OR 1000 Hz)			55 mΩ MAX.			X	-
INSULATION RESISTANCE		250 V DC			100 MΩ MIN.			X	-
VOLTAGE PROOF		300 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN			X	-
<b>MECHANICAL CHARACTERISTICS</b>									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE: 70 N MAX. WITHDRAWAL FORCE: 6.5 N MIN.			X	-
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm FOR 2 h IN 3 DIRECTIONS.			1) NO ELECTRICAL DISCONTINUITY OF 1 μs 2) CONTACT RESISTANCE: 55 mΩ MAX. 3) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
SHOCK		490 m/s <sup>2</sup> DURATION OF PULSE 11 ms FOR 3 TIMES IN 3 DIRECTIONS.						X	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) INSULATION RESISTANCE:			X	-
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+5~+35→+85→+5~+35°C TIME 30→10~15→30→10~15 min. UNDER 5 CYCLES.			100 MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO HEAVY CORROSION.			X	-
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA-38)						X	-
<b>REMARKS</b>									
				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				<i>K. Kiriyama</i>	<i>H. Yamaguchi</i>	<i>H. Okawa</i>	<i>Y. Yoshimura</i>		
				01.04.24	01.04.25	01.04.25	01.04.25		
UNLESS OTHERWISE SPECIFIED, REFER TO JIS C 5402.									
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST x: APPLICABLE TEST									
<b>HRS</b> HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO.		
CODE NO.(OLD)				DRAWING NO.			CODE NO.		
CL				ELC4-150676-01			FX8-100S-SV(23)		
							1		
							1		

TO
PCK

