XS8C4A4PCN12

Inductive proximity sensors XS, inductive sensor XS8 40x40x117, PBT, Sn40 mm, 12...48 VDC, terminals





Main

Range of Product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor Type	Inductive proximity sensor
Device Application	Mobile equipment
Sensor name	XS8
Sensor design	Form 40 x 40 x 117
Size	117 mm
Body type	Fixed
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Enclosure Material	PBT
Type of output signal	Discrete
Wiring Technique	4-wire
[Sn] nominal sensing distance	1.57 in (40 mm)
Discrete output function	1 NO + 1 NC
Output circuit type	DC
Discrete output type	PNP
Electrical connection	Screw-clamp terminals, 4 x 1.5 mm ²
[Us] rated supply voltage	1248 V DC reverse polarity protection
Switching capacity in mA	<= 200 mA overload and short-circuit protection
IP degree of protection	IP67 conforming to IEC 60529 IP65 conforming to IEC 60529 IP69K conforming to DIN 40050

Complementary

SIL 2 EN/IEC 61508 PL = d EN/ISO 13849-1 SILCL 2 IEC 62061
MTTFd = 1546 years PFHd = 7.4E-8 1/h SFF = 92 % DC = 75 % with appropriate safety controller
5 positions turret head
PBT
0.001.26 in (032 mm)
315% of Sr
<= 3% of Sr
1 tapped entry 1/2" NPT cable gland
Supply on 1 LED green) Output state 1 LED yellow)
1058 V DC
<= 200 Hz
<2 V closed)
015 mA no-load
7.5 ms

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not inherent or and is not to be used for determining suitability or inhability of these products for specific user applications. This documentation is not integrated to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Maximum delay response	1.4 ms	
Maximum delay recovery	2.5 ms	
Marking	CE	
Height	1.57 in (40 mm)	
Length	1.57 in (40 mm)	
Width	4.61 in (117 mm)	
Net Weight	0.54 lb(US) (0.244 kg)	
Environment		
Product Certifications	UL	
	CSA	

Product Certifications	UL	
	CSA	
	TÜV	
	CCC	
	E2	
Ambient air temperature for operation	-13158 °F (-2570 °C)	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Vibration resistance	25 gn +/- 2 mm 1055 Hz)IEC 60068-2-6	
Shock resistance	50 gn 11 msEN 60068-2-27	

Ordering and shipping details

0 11 0	
Category	22486 - SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	3389119058322
Nbr. of units in pkg.	1
Package weight(Lbs)	8.61 oz (244 g)
Returnability	Yes
Country of origin	FR

Packing Units

•		
Unit Type of Package 1	PCE	
Package 1 Height	5.71 in (14.5 cm)	
Package 1 width	1.97 in (5 cm)	
Package 1 Length	1.97 in (5 cm)	

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	[™] REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEN RoHS Declaration
Mercury free	Yes
RoHS exemption information	₽¥Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Contraction Warranty	
Warranty	18 months