

Description

The XP151A13A0MR uses advanced trench technology

to provide excellent $R_{\text{DS}(\text{ON})}$, low gate charge and

operation with gate voltages as low as 2.5V.

This device is suitable for use as a Battery

protection or in other Switching application.



SOT-23

General Features

 $V_{DS} = 20V I_{D} = 2.3 A$


 $R_{DS(ON)}$ < 60m Ω @ V_{GS} =4.5V

Application

Battery protection

Load switch

Uninterruptible power supply



N-Channel MOSFET

Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
XP151A13A0MR	SOT-23	HXY MOSFET	3000

Absolute Maximum Ratings (T_A=25 ℃ unless otherwise noted)

Parameter	Limit	Unit
Drain-Source Voltage	20	V
Gate-Source Voltage	±12	V
Drain Current-Continuous	2.3	A
Drain Current-Pulsed (Note 1)	16	A
Maximum Power Dissipation	0.9	W
Operating Junction and Storage Temperature Range	-55 To 150	${\mathbb C}$
Thermal Resistance,Junction-to-Ambient (Note 2)	139	°C/W
	Drain-Source Voltage Gate-Source Voltage Drain Current-Continuous Drain Current-Pulsed (Note 1) Maximum Power Dissipation Operating Junction and Storage Temperature Range	Drain-Source Voltage 20 Gate-Source Voltage ±12 Drain Current-Continuous 2.3 Drain Current-Pulsed (Note 1) 16 Maximum Power Dissipation 0.9 Operating Junction and Storage Temperature Range -55 To 150




Electrical Characteristics (T_A=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	20	22	-	V
Zero Gate Voltage Drain Current	IDSS	V _{DS} =20V,V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	Igss	V _{GS} =±12V,V _{DS} =0V	-	-	±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} ,I _D =250μA	0.5	0.75	1.2	V
	Rds(on)	V _{GS} =2.5V, I _D =2.0A	-	54	72	mΩ
Drain-Source On-State Resistance		V _{GS} =4.5V, I _D =2.3A	-	48	60	mΩ
Forward Transconductance	g FS	V _{DS} =5V,I _D =2.3A	-	8	-	S
Input Capacitance	C _{lss}		-	260	-	PF
Output Capacitance	Coss	V _{DS} =10V,V _{GS} =0V,	-	48	-	PF
Reverse Transfer Capacitance	C _{rss}	F=1.0MHz	-	27	-	PF
Turn-on Delay Time	td(on)		-	2.5	-	nS
Turn-on Rise Time	tr	V _{DD} =10V, R _L =3.3Ω	-	3.2	-	nS
Turn-Off Delay Time	td(off)	V_{GS} =4.5V, R_{GEN} =6 Ω	-	21	-	nS
Turn-Off Fall Time	t _f		-	3	-	nS
Total Gate Charge	Qg		-	2.9	5	nC
Gate-Source Charge	Q _{gs}	V _{DS} =10V,I _D =2.3A,	-	0.4	-	nC
Gate-Drain Charge	Q _{gd}	V _{GS} =4.5V	-	0.6	-	nC
Diode Forward Voltage (Note 3)	VsD	V _{GS} =0V,I _S =2.3A	-	0.75	1.2	V
Diode Forward Current (Note 2)	Is		-	-	3.3	Α

Notes:

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature.
- 2. Surface Mounted on FR4 Board, t ≤ 10 sec.
- 3. Pulse Test: Pulse Width ≤ 300µs, Duty Cycle ≤ 2%.
- 4. Guaranteed by design, not subject to production



Typical Electrical and Thermal Characteristics




Figure 1:Switching Test Circuit




Figure 2:Switching Waveforms




Figure 3 Power Dissipation





Figure 4 Drain Current







Figure 6 Drain-Source On-Resistance







Figure 7 Transfer Characteristics



Vgs Gate-Source Voltage (V)
Figure 9 Rdson vs Vgs




Figure 11 Gate Charge






Figure 8 Drain-Source On-Resistance



Vds Drain-Source Voltage (V)

Figure 10 Capacitance vs Vds





Vsd Source-Drain Voltage (V)


Figure 12 Source- Drain Diode Forward



SOT-23 Package Outline Dimensions








Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950	TYP	0.037 TYP		
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022 REF		
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

SOT-23 Suggested Pad Layout



Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:± 0.05mm.
 3.The pad layout is for reference purposes only.



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.