

General Description

The AO8820 is the highest performance trench

N-ch MOSFETs with extreme high cell density,

which provide excellent RDSON and gate charge

for most of the small power switching and

load switch applications. The meet the RoHS and

Product requirement with full function reliability approved.




TSSOP-8

General Features

 $V_{DS} = 20V I_{D} = 7A$

 $R_{DS(ON)}$ < 14m Ω @ V_{GS} =4. 5V

 $R_{DS(ON)}$ < 17m Ω @ V_{GS}=2. 5V



Application

Battery protection

Load switch

Uninterruptible power supply

Dual N-Channel MOSFET

Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
AO8820	TSSOP-8	HXY MOSFET	5000

Absolute Maximum Ratings (TA=25 ℃ unless otherwise noted)

Symbol	Parameter	Limit	Unit
V _{DS}	Drain-Source Voltage	20	V
Vgs	Gate-Source Voltage	±10	V
I _D	Drain Current-Continuous	7	А
Ірм	Drain Current-Pulsed (Note 1)	23	А
P _D	Maximum Power Dissipation	1.25	W
T _J ,T _{STG}	Operating Junction and Storage Temperature Range	-55 To 150	$^{\circ}$
Reja	Thermal Resistance,Junction-to-Ambient (Note 2)	111	°C/W



Electrical Characteristics (T_A=25°C unless otherwise noted)

Parameter Symbol Condition		Condition	Min	Тур	Max	Unit
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250µA	20	-	-	V
Zero Gate Voltage Drain Current	Ipss	V _{DS} =16V,V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	lgss	V _{GS} =±8V,V _{DS} =0V	-	-	±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} ,I _D =250μA	0.5	0.7	1.2	V
		V _{GS} =4.5V, I _D =4.5A	-	12	14	mΩ
Drain-Source On-State Resistance	RDS(ON)	V _{GS} =2.5V, I _D =3.5A	-	15	17	mΩ
Forward Transconductance	gFS	V _{DS} =5V,I _D =3.5A	-	20	-	S
Input Capacitance	C _{lss}		-	955	-	PF
Output Capacitance	Coss	V _{DS} =8V,V _{GS} =0V,	-	200	-	PF
Reverse Transfer Capacitance	Crss	F=1.0MHz	-	150	-	PF
Turn-on Delay Time	td(on)		-	8		nS
Turn-on Rise Time	tr	V _{DD} =10V,I _D =3.5A	-	17	-	nS
Turn-Off Delay Time	t _{d(off)}	$V_{GS}=1.5V,R_{GEN}=6\Omega$	-	27	-	nS
Turn-Off Fall Time	t _f		-	8.8	-	nS
Total Gate Charge	Qg		-	11.3	-	nC
Gate-Source Charge	Q _{gs}	V _{DS} =10V,I _D =7A,	-	1.89	-	nC
Gate-Drain Charge	Q_gd	V _{GS} =4.5V	-	3.56	-	nC
Diode Forward Voltage (Note 3)	Vsp	V _{GS} =0V,I _S =1.7A	-	0.75	1.2	V
Diode Forward Current (Note 2)	Is		-	-	7	Α

Notes:

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature.
- 2. Surface Mounted on FR4 Board, t ≤ 10 sec.
- **3.** Pulse Test: Pulse Width ≤ 300μ s, Duty Cycle ≤ 2%.
- 4. Guaranteed by design, not subject to production



Typical Characteristics

Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3:On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics






Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature







Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient






TSSOP-8 Package Outline Dimensions







Symbol	Dimensions	Dimensions In Millimeters		Dimensions In Inches		
Symbol	Min	Max	Min	Max		
D	2.900	3. 100	0.114	0.122		
Е	4.300	4. 500	0. 169	0.177		
b	0.190	0.300	0.007	0.012		
С	0.090	0.200	0.004	0.008		
E1	6. 250	6. 550	0. 246	0.258		
A		1. 200		0.047		
A2	0.800	1.000	0.031	0.039		
A1	0.050	0.150	0.002	0.006		
e	0. 65	0.65 (BSC)		0. 026 (BSC)		
L	0.500	0. 700	0.020	0.028		
Н	0.25(T	0.25(TYP)		0.01(TYP)		
θ	1°	7°	1 °	7°		



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.