







ESD	Features
 	<ul style="list-style-type: none"> ✧ Transient protection for high-speed data lines IEC 61000-4-2(ESD) ±25KV(Air) ±20KV(Contact) IEC 61000-4-4(EFT)40A(5/50ns) Cable Discharge Event(CDE) ✧ Package optimized for high-speed lines ✧ Ultra-small package(2.5mm*1.0mm*0.50mm) ✧ Protects four data lines ✧ Low capacitance:0.2pF for each channel ✧ Low leakage current ✧ Low clamping voltage ✧ Each I/O pin can withstand over 1000 ESD strikes for ±8KV contact discharge
<p>MACHANICAL DATA</p> <ul style="list-style-type: none"> ✧DFN2510 package ✧Flammability Rating: UL 94V-0 ✧Terminal: Matte tin plated. ✧Packaging: Tape and Reel ✧High temperature soldering guaranted:260°C/10s ✧Reel size: 7 inch <p>ORDERING INFORMATION</p> <ul style="list-style-type: none"> ✧ Device:ESD0524P ✧Package: DFN2510 ✧Marking: T54SP ✧Material: Halogen free ✧Packing: Tape & Reel ✧Quantity per reel: 3,000pcs 	<p>APPLICATIONS</p> <ul style="list-style-type: none"> ✧Serial ATA ✧PCI Express ✧Desktops, Servers and Notebooks ✧MDDI Ports ✧USB 2.0/3.0 and Data Line Protection ✧Display Ports ✧High Definition Multi-Media Interface (HDMI) ✧Digital Visual Interface (DVI)

ABSOLUTE MAXIMUM RATING			
Symbol	Parameter	Value	Units
P _{PP}	Peak Pulse Power(8/20μs)	100	W
V _{ESD}	ESD per IEC 61000-4-2 (Air)	±25	kV
	ESD per IEC 61000-4-2 (Contact)	±20	
T _{OPT}	Operating Temperature	-55/+125	°C
T _{STG}	Storage Temperature	-55/+150	°C


ELECTRICAL CHARACTERISTICS (T _{amb} =25. °C)						
Symbol	Parameter	Test Condition	Min	Typ	Max	Units
V _{RWM}	Reverse Working Voltage	Any I/O pin to GND			5.0	V
V _{BR}	Reverse Breakdown Voltage	I _r = 1mA Any I/O pin to GND	6.0		10.0	V
I _R	Reverse Leakage Current	V _{RWM} = 5V Any I/O pin to GND			1.0	μA
V _C	Clamping Voltage	I _{PP} = 1A, t _p = 8/20μs Any I/O pin to GND			15	V
		I _{PP} = 4A, t _p = 8/20μs Any I/O pin to GND			25	V
C _{ESD}	Parasitic Capacitance	V _R = 0V, f = 1MHz Between I/O and GND		0.2	0.25	pF
C _{ESD}	Parasitic Capacitance	V _R = 0V, f = 1MHz Between I/O and I/O		0.2	0.25	pF

Note: I/O pins are pin 1,2,4,5, GND pins are pin 3,8.

ELECTRICAL CHARACTERISTICS CURVE



DFN2510 PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions (mm)	
	Nom.	Max.
D	2.50	2.55
E	1.00	1.05
b1	0.40	0.45
b2		
b	0.20	0.25
L	0.38	0.43
Nd		
e		
R	0.125	0.15
A	0.50	0.55
c		
A1	-	0.05