



1-Line Bidirectional ESD Protection Diode


DFN1006-2L

### Schematic & Pin configuration

Simplified outline

1                  2

Graphic symbol



### General description

Low capacitance bidirectional ElectroStatic Discharge (ESD) protection diode in a DFN1006 (SOD882) leadless ultra small Surface-Mounted Device (SMD) plastic package designed to protect one signal line from the damage caused by ESD and other transients.

### Features and benefits

- Bidirectional ESD protection of one line
- Low operating voltage: 5.0V
- Low clamping voltage  $V_c = 10$  V@50A
- Response time is typically < 1 ns
- Ultra Low Leakage: nA Level
- IEC 61000-4-2; level 4 (ESD)
- IEC 61000-4-5 (surge); 1ppm = 50 A

### Application information

- Portable electronics
- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- Communication systems
- Power supplies

**Maximum Ratings** (Top=25°C,unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (Tp=8/20 μ s)	PppM	600	W
Rated Peak Pulse Current (Tp=8/20 μ s)	IppM	50	A
Maximum lead temperature for soldering during 10s	Tt	260	°C
Storage Temperature Range	Tstg	-55 to +150	°C
Operating Temperature Range	Top	-40 to +125	°C
Maximum junction temperature	Tj	150	°C
ESD voltage IEC 61000-4-2(air discharge)	VESD	30	kV
ESD voltage IEC 61000-4-2 (contact discharge)	VESD	30	kV

**Electrical Characteristics** (Top=25°C,unless otherwise specified)


Parameter	Symbol	Min	Typ	Max	Unit	Condition
Reverse Working Voltage	VRWM			5.0	V	
Breakdown Voltage	VBR	6.5		7.0	V	Ir=1mA
Leakage Current ILeak	Ik			100	nA	VRwm=5.0V
Clamping Voltage	Vc		7.5	9.0	V	1pp=1.0A, Tp=8/20 μ s
Clamping Voltage	Vc		10.0	12	V	pp=50A, Tp=8/20 μ s
Junction Capacitance	Cj		100	120	pF	VR=0V, f=1MHz

**Portion Electronics Parameter**


Symbol	Parameter
Ipp	Maximum Reverse Peak Pulse Current
Vc	Clamping Voltage @1pp
VgwM	Working Peak Reverse Voltage
Ir	Maximum Reverse Leakage Current @VgwM
r	Test Current
VBR	VBR Breakdown Voltage @r




### Typical Performance Characteristics ( $T_a=25^\circ\text{C}$ unless otherwise Specified)




**IEC61000-4-2 Pulse Waveform**




**IEC61000-4-58X20μs Pulse Waveform**




**Junction Capacitance vs. Reverse Voltage**



**Clamping Voltage vs. Peak Pulse Current**



**Peak Pulse Power vs. Pulse Time**




**Ambient Temperature  $T_a$ (°C)**

**Power Derating Curve**

## Package Outline Dimensions

DFN1006-2L



DFN1006-2L (mm)			
Dim	Min	Typ.	Max
A	0.45	0.50	0.55
A1	0	0.02	0.05
b	0.45	0.5	0.55
C	0.1	0.15	0.18
D	0.95	1.00	1.05
E	0.55	0.60	0.65
L	0.20	0.25	0.30
L1	0.035	0.05	0.065