


- Omni-directional Pattern
 High Efficiency of 70 ~ 80 %
- Surface mount component

- Location based services
- Personal Area Networks (PAN)
- Short range, high speed data links for Medical and Commercial equipment

Product Dimensions



6.24 ~ 8.50 GHz UWB - Chip Antenna



ACR0301U

Request Samples 🕥

Check Inventory

3.2 x 1.6 x 1.1 mm RoHS/RoHS II Compliant MSL Level = 1

Electrical Specification

Pa	arameter	Specification			Unit	
		Min	Тур	Max	Onit	
Operating Frequency 6.24			8.5	CII-		
Center Frequency			7.37		GHz	
VSWR				2.0		
Polarization		Linear				
Peak Gain				4.5	dBi	
Efficiency			$70 \sim 80$		%	
Ir	Impedance		50		Ω	
Azimuthal Beamwidth		Omni-directional				
Input	Continuous			3	- W	
Power	Up to 5 minutes			5	W	

<u>Note</u>: All test measurements were conducted with the antenna on a 42.6x22.6 mm Evaluation board. Please note that the performance is dependent on the ground plane dimensions, matching network and application environment.

Mechanical Specification

Parameter	Specification	
Antenna Dimension	3.2 x 1.6 x 1.1 mm	
Antenna Ground Clearance Area	8 x 7.8 mm	
Evaluation board Dimension	42.6 x 22.6 x 0.8 mm	
Manufacturing Technology	Multilayer LTCC Chip	
Mounting Type	Surface Mount	


Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	+5°C to +40°C
Relative Humidity	30 ~ 70 %
Pb-free	Yes



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21




Unit: mm



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21



Unit : mm



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com


REVISED: 07-19-21






5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21





6.24 ~ 8.50 GHz UWB - Chip Antenna



ACR0301U

Request Samples 🕥

Check Inventory

3.2 x 1.6 x 1.1 mm RoHS/RoHS II Compliant MSL Level = 1

Reliability Test

Items	Test Method	Standard	
Resistance to soldering heat JIS C 0050-5.4	 Preheating temperature: 120 ~ 150 °C Duration: 1 min Solder Temperature: 270 ± 5 °C Immersion Time: 10 ± 1 s Solder: Sn3Ag0.5Cu for lead free Measurement to be made after keeping at room temperature for 24 ± 2 hrs 	 Specimens shall be free of any traffic discontinuities during the test. (No mechanical damage) The appearance of the product, and electrical properties to meet the requirements under operational temperature range within -40 ~ +85 °C Loss of metallization on the edges of each electrode shall not exceed 25% 	
Solderability JIS C 0050-4.6 JESD22-B102D	 Solder bath temperature : 235 +/- 5 C Immersion time : 2 ± 0.5 sec Solder : Sn3Ag0.5Cu for lead-free 	At least 95% of a surface of each terminal electrode must be covered by fresh solder.	
Adhesive Strength of Termination JIS C 0051- 7.4.3	 Pressurizing force : 5N (LGA terminal series) ; 5N(≤0603) ; 10N(>0603) Test time : 10±1 s 	No remarkable damage or removal of the termination.	
Vibration JIS C 0040	 Vibration Frequency: 10~50~10 Hz (1min) Amplitude:1.5 mm Sweep Direction: 6 Hrs = X(2H), Y(2H), Z(2H) Examine the appearance and functions after the test. 	1. Specimens shall be free of any traffic	
Drop Test JIS C 0044	 Drop the object onto a concrete surface or steel surface from a height of 75 cm. Number of Times : 6 surfaces for each unit – 2 times each side. Examine the appearance and functions after the test. 	 discontinuities during the test. (No mechanical damage) 2. The appearance of the product, and electrical properties to meet the requirements under operational temperature range within -40 ~ 	
Bending test1. The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm/s per second until the deflection becomes 1mm/s and then pressure shall be maintained for 5 ± 1 sec.2. Measurement to be made after keeping at room temperature for 24±2 hours		+85 °C	



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21

6.24 ~ 8.50 GHz UWB - Chip Antenna



ACR0301U

Request Samples 🕥

Check Inventory

3.2 x 1.6 x 1.1 mm RoHS/RoHS II Compliant MSL Level = 1

Temperature cycle JIS C 0025	 30±3 minutes at -40°C±3°C 10~15 minutes at room temperature 30±3 minutes at +85°C±3°C 10~15 minutes at room temperature Number of cycles: 100 continuous cycles Measurement to be made after keeping at room temperature for 24±2 hrs 	
High Temperature JIS C 0021	 Temperature: 85°C±2°C Time: 1000+24/-0 H Examine the appearance and functions after taken out at room temperature for 24±2H. 	 Specimens shall be free of any traffic discontinuities during the test. (No mechanical damage) The appearance of the product, and electrical properties to meet the requirements under operational temperature range within -40 ~ +85 °C
Low Temperature JIS C 0020	 Temperature: -40°C±2°C Time: 1000+24/-0 H Examine the appearance and functions after taken out at room temperature for 24±2H. 	
Humidity (Steady conditions) JIS C 0022	 Temperature range: 40°C±2°C Humidity Range: 90%~95% R.H. Cycle times: 1000+24/-0 H Examine the appearance and functions after taken out at room temperature for 24H±2H. 500 hrs measuring the first data then 1000 hrs data. 	




5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21

6.24 ~ 8.50 GHz UWB - Chip Antenna ACR0301U Request Samples () Check Inventory () 3.2 x 1.6 x 1.1 mm RoHS/RoHS II Compliant MSL Level = 1

Infrared Soldering Profile

A typical example of soldering processes that provides reliable joints without any damage is given below. This product can sustain a reflow process three times, and at temperatures below 260 °C.




Caution


- Do not place the product in a corrosive or corrosive gas environment as it may cause oxidation of the metal electrode, resulting in poor solderability.
- Products should be stored on the palette for the prevention of the influence from external factors including humidity, dust.
- Products should be stored in an environment without being exposed to but not limited to heat shock, vibration, direct sunlight.
- Products should be stored in an airtight packaged condition.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21






Dimension	Specification (mm)
А	D178
В	D60
С	D13.5



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 07-19-21