

ESDL5V0BOE


Description

ESDL5V0BOE is a bi-directional TVS. It has been specifically designed to protect the sensitive electronic components which are connected to low speed data lines and control lines from over-stress caused by ESD (Electrostatic Discharge), EFT (Electrical Fast Transients) and Lightning.

ESDL5V0BOE may be used to provide ESD protection up to $\pm 30\text{KV}$ according to IEC61000-4-2, and withstand peak pulse current up to 8A (8/20 μs) according to IEC61000-4-5.

ESDL5V0BOE is available in SOD-523 package. Standard products are Pb-free and Halogen-free.

SOD-523



Pin configuration



Marking



Features

- ◆ Stand-off voltage: $\pm 5\text{V}$ Max.
- ◆ Transient protection for each line according to IEC61000-4-2(ESD): $\pm 30\text{kV}$ (contact)
IEC61000-4-4 (EFT): 40A (5/50ns)
IEC61000-4-5(surge): 8A (8/20 μs)
- ◆ Ultra-low capacitance: $C_J = 10\text{pF}$ typ.
- ◆ Low leakage current:
- ◆ Low clamping voltage: $V_{CL} = 10.0\text{V}$ typ. @ $I_{PP} = 16\text{A}$ (TLP)
- ◆ Solid-state silicon technology

Applications

- ◆ Cellular phones
- ◆ Tablets
- ◆ Laptops
- ◆ Other portable devices
- ◆ Network communication devices

Order information

Device	Package	Shipping
ESDL5V0BOE	SOD-523	3000/Tape&Reel

Absolute Maximum Ratings

Parameter	Symbol	Value	Units
Peak pulse power (tp = 8/20us)	P_{PK}	96	W
Peak pulse current (tp = 8/20us)	I_{PP}	8	A
IEC61000-4-2 (Contact)	V_{ESD}	± 30	kV
IEC61000-4-2 (Air)	V_{ESD}	± 30	kV
Lead Temperature	T_L	260	$^{\circ}\text{C}$
Operating temperature	T_{OP}	-40 to 85	$^{\circ}\text{C}$
Junction Temperature	T_J	125	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^{\circ}\text{C}$

ESDL5V0BOE

Electrical Characteristics (T =25°C)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-off voltage	V_{RWM}				± 5.0	V
Reverse Breakdown voltage	V_{BR}	$I_t=1\text{ mA}$	5.3	6		V
Reverse Leakage Current	I_R	$V_{RWM}=5.0\text{ V}$			100	nA
Reverse holding voltage	V_{HOLD}	$I_{HOLD}=50\text{ mA}$	5.3	6		V
Clamping voltage ¹⁾	V_{CL}	$I_{PP}=16\text{ A}, tp=100\text{ ns}$		10.0		V
Dynamic resistance ¹⁾	R_{DYN}			0.2		Ω
Clamping voltage ²⁾	V_{CL}	$V_{ESD}= 8\text{ kV}$		10.0		V
Clamping voltage ³⁾	V_{CL}	$I_{PP}=1\text{ A}, tp=8/20\mu\text{s}$			8	V
		$I_{PP}=8\text{ A}, tp=8/20\mu\text{s}$			12	V
Junction Capacitance	C_J	$V_R=0\text{ V}, f=1\text{ MHz}$		10	13	pF
		$V_R=2.5\text{ V}, f=1\text{ MHz}$		8	11	pF


Notes:

1)TLP parameter: $Z_0 = 50\Omega$, $tp = 100\text{ ns}$, $tr = 2\text{ ns}$, averaging window from 60ns to 80ns. RDYN is calculated from 4A to 16A.

2)Contact discharge mode, according to IEC61000-4-2.


3)Non-repetitive current pulse, according to IEC61000-4-5.

Electrical Characteristics




ESDL5V0BOE


Typical characteristics(TA=25°C,unless otherwise noted)




8/20 μ s waveform per IEC61000-4-5
Capacitance vs. Reverse voltage




Clamping voltage vs. Peak pulse current




Contact discharge current waveform per IEC61000-4-2



Capacitance vs. Reverse voltage




Non-repetitive peak pulse power vs. Pulse time




Power derating vs. Ambient temperature


ESDL5V0BOE



ESD clamping
(+8kV contact discharge per IEC61000-4-2)




ESD clamping
(-8kV contact discharge per IEC61000-4-2)



ESDL5V0BOE

Package Outline

SOD-523



Symbol	Dimensions in millimeter		
	Min.	Typ.	Max.
A	0.510	0.640	0.770
A1	0.500	0.600	0.700
b	0.250	0.300	0.350
c	0.080	0.115	0.150
D	0.750	0.800	0.850
E	1.100	1.200	1.300
E1	1.500	1.600	1.700
E2	0.200 Ref		
L	0.010	0.040	0.070
θ	7° Ref		

Recommend land pattern (Unit: mm)

