

### Description

The DMP510DL uses advanced trench technology and design to provide excellent  $R_{DS(ON)}$  with low gate charge. It can be used in a wide variety of applications.

### **General Features**


 $V_{DS} = -50V, I_D = -0.1A$  $R_{DS(ON)} < 5 \Omega @ V_{GS} = -10V$  $R_{DS(ON)} < 6 \Omega @ V_{GS} = -4.5V$ 

# Application

Power switching application Hard switched and high frequency circuits DC-DC converter








P-Channel MOSFET

### Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
DMP510DL	SOT-23	HXY MOSFET	3000

### Absolute Maximum Ratings (T<sub>A</sub>=25℃unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	Vds	-50	V
Gate-Source Voltage	Vgs	±20	V
Drain Current-Continuous	Ι <sub>D</sub>	-0.1	А
Pulsed Drain Current	I <sub>DM</sub>	-0.5	А
Maximum Power Dissipation	PD	0.35	W
Operating Junction and Storage Temperature Range	T <sub>J</sub> ,T <sub>STG</sub>	-55 To 150	°C
Thermal Resistance ,Junction-to-Ambient <sup>(Note 2)</sup>	R <sub>0JA</sub>	62.5	°C/W



### Electrical Characteristics (Ta=25°C unless otherwise specified)

Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
Static						
V <sub>(BR)DSS</sub>	Drain-source breakdown voltage	V <sub>GS</sub> =0, I <sub>D</sub> =250µA	-50			V
V <sub>GS(th)</sub>	Gate threshold voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =-250µA	-0.8		-2.0	V
I <sub>GSS</sub>	Gate-body leakage current	$V_{DS}=0, V_{GS}=\pm 10V$			±10	μA
I <sub>DSS</sub>	Zero gate voltage drain current	V <sub>DS</sub> =-50V, V <sub>GS</sub> =0V			-10	μA
		V <sub>DS</sub> =-40V, V <sub>GS</sub> =0V			-100	nA
R <sub>DS(on)</sub>	Drain-source on-resistance <sup>a</sup>	V <sub>GS</sub> =-10V, I <sub>D</sub> =-0.13A		2	5	Ω
		V <sub>GS</sub> =-4.5V, I <sub>D</sub> =-0.13A		2.5	6	Ω
<b>g</b> fs	Forward transconductance <sup>a</sup>	V <sub>DS</sub> =-25V, I <sub>D</sub> =-0.13A	<sub>D</sub> =-0.13A 50			mS
$V_{\text{SD}}$	Diode forward voltage	I <sub>S</sub> =-0.13A,V <sub>GS</sub> =0V			-1.0	V
Dynamic						
Ciss	Input capacitance			25		
Coss	Output capacitance	V <sub>DS</sub> =-25V, V <sub>GS</sub> =0V, f=1MHz		15		pF
Crss	Reverse transfer capacitance <sup>b</sup>			3.5		
Switching	J <sup>b</sup>					
t <sub>d(on)</sub>	Turn-on delay time			16.7		
tr	Rise time	V <sub>GS</sub> =-10V,V <sub>DS</sub> =-15V		8.6		nS
t <sub>d(off)</sub>	Turn-off delay time	$I_D$ =-200mA, $R_{GEN}$ =25 $\Omega$		17.9		113
t <sub>f</sub>	Fall time			5.3		]

Notes :

a. Pulse Test : Pulse width≤300µs, duty cycle ≤2%.b. Guaranteed by design, not subject to producting.



# DMP510DL P-Channel Enhancement Mode MOSFET









Figure1. Output Characteristics










Figure 2. Transfer Characteristics




Figure4. Drain-Source on Resistance







Figure6. Gate Threshold vs. Junction Temperature



# **SOT-23 Package Outline Dimensions**








Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950 TYP		0.037 TYP		
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022 REF		
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

# SOT-23 Suggested Pad Layout



Note: 1.Controlling dimension: in millimeters.

2.General tolerance:± 0.05mm.
 3.The pad layout is for reference purposes only.



#### **Attention**

• Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

• HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

• Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could

give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

• In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

• No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production.
HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.