

	安	产(Custom	ner) ·			
		Ouston				
承认书	1 01 .					
Approva	1 Sheet					
谨致执事者:		之有关详细规格 -份附有贵公司			•	
-		ou herewith on y "Approval she	-		_	pproval.
型号 (Model	No.) :	A-SA3HR	314GG	SW026-H22		
发文日期(Is	sue Date):_	2017/12/12	_ 承认	日期(Appro	ved Date):_	
Checking	signature of	Amicc	_	Approval	signature of	customer
Designer	Checker	Approver		Designer	Checker	Approver
Allen						
江苏欧密格:	光电科技股份有	限公司				
Jiangsu Ami 地址:江苏	cc Opto-Electro 省常州市武进区	onics Technolog 武南中路 98 号 ijin, Changzhou				

TEL:0086-519-89806966 FAX:0086-519-86523668

# Lamp LED Type ■ Ф3mm LED LAMP

## A-SA3HR314GGW026-H22



#### **Features**

- Ф3mm LED LAMP
- Wide viewing angle
- Pb-free
- RoHS compliant

## **Description**

The Amicc LAMP package has high efficacy, high power consumption, wide viewing angle and a compact form factor. These features make this package an ideal LED for all lighting applications.

## **Applications**

- General lighting
- · Decorative and Entertainment Lighting
- Indicators
- Automotive Telecommunication
- · Switch lights

## **Device Selection Guide**

Chip Materials	Emitted Color	Resin Color
GaP/GaP	Green	White Diffused



## Absolute Maximum Ratings (Tsoldering=25℃)

Parameter	Symbol	Rating	Unit
Forward Current	l <sub>F</sub>	30	mA
Peak Forward Current (Duty 1/10 @1ms)	I <sub>FP</sub>	100	mA
Power Dissipation	Pd	78	mW
Reverse Voltage per chip	Vr	5	V
Operating Temperature	$T_{opr}$	-40 ~ +85	$^{\circ}$
Storage Temperature	T <sub>stg</sub>	-40 ~ +85	$^{\circ}$

#### Note:

The products are sensitive to static electricity and must be carefully taken when handling products.

## Electro-Optical Characteristics (T<sub>Soldering</sub>=25°C)


Parameter	Symbol	Color	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv			8.0		mcd	I <sub>F</sub> =20mA
Peak Wavelength	$\lambda_{\mathrm{p}}$			567		nm	I <sub>F</sub> =20mA
Dominant Wavelength	$\lambda_{ m d}$			572		nm	I <sub>F</sub> =20mA
Forward Voltage	VF			2.0	2.4	V	I <sub>F</sub> =20mA
Viewing Angle	201/2			70		deg	I <sub>F</sub> =20mA
Reverse Current	I <sub>R</sub>				100	μА	V <sub>R</sub> =5V


#### Notes:


- 1. Tolerance of Luminous Intensity ±10%.
- 2. Tolerance of Dominant Wavelength: ±1nm
- 3. Tolerance of Forward Voltage: ±0.1V.




## **Typical Electro-Optical Characteristics Curve**









FORWARD CURRENT VS. AMBIENT TEMPERATURE

4



## **Bin Range of Luminous Intensity**

Bin Code	Min.	Max.	Unit	Condition
В0	5	10		
B1	10	20	mcd	I <sub>F</sub> =20mA
B2	20	30		

Note:

Tolerance of Luminous Intensity: ±10%.

## **Bin Range of Dominant Wavelength**

Bin Code	Min.	Max.	Unit	Condition
G1	565	570	_	
G2	570	575	nm	I <sub>F</sub> =20mA
G3	575	580		

Note:

Tolerance of Dominant Wavelength: ±1nm.


## **Bin Range of Forward Voltage**

Bin Code	Min.	Max.	Unit	Condition
A0	1.8	2.0	_	
A1	2.0	2.2	V	I <sub>F</sub> =20mA
A2	2.2	2.4		

Note:

Tolerance of Forward Voltage:  $\pm$  0.1V.

## **Package Dimension**




## Note:

- 1.All Dimensions are in millimeters.
- 2. Tolerance is  $\pm 0.25$  mm unless otherwise specified.
- 3. The color of holder: Black.
- 4. The material of holder: N66.



## **Moisture Resistant Packing Materials**

## **Label Explanation**



·CPN: Customer's Product Number


·P/N: Product Number

·TYPE :Part NO.

·IV: Luminous Intensity Rank ·WD: Dom. Wavelength Rank ·VF: Forward Voltage Rank

·LOT NO.: Lot Number ·QTY: Packing Quantity

## Moisture Resistant Packing Process: 500 PCS/Bag





Reliability Test Items and Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Wave Soldering	T, sol:260°C/5sec	3 min. Max.	22PCS	0/1
2	Solderability	T, sol:230°C/5sec	60 sec. Max.	22PCS	0/1
3	Thermal Shock	H:+105°C 10min ∫ L:-55°C 10min	10 Cycles	22 PCS.	0/1
4	Temperature Cycle	H: +105 $^{\circ}$ C 30min $ \int 25 ^{\circ}$ C 5min $ \int L: -55 ^{\circ}$ C 30min $ \int 25 ^{\circ}$ C 5min	10 Cycles	22 PCS.	0/1
5	High Temperature/Humidity Reverse Bias	Ta=65℃,90%RH	240 Hrs.	22 PCS.	0/1
6	DC Operation Life	Ta=25℃, I <sub>F</sub> = 20 mA	1000 Hrs.	22 PCS.	0/1



#### **Precautions for Use**

1. Over-current-proof

Customer must apply resistors for protection; otherwise slight voltage shift will cause big current change (Burn out will happen).

## 2. Storage


- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at  $30^{\circ}$ C or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30 ℃ or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

  Baking treatment: 60±5℃ for 24 hours.

#### 3. Soldering

Method	Remark
Hand Soldering	Soldering time: 3 sec MAX.     Distance: 3 mm MIN (from solder joint to case)
DIP Soldering	1. Preheat temp: 100 °C MAX, 60 sec MAX. 2. Bath temp: 260 °C MAX. 3. Bath time: 5 sec MAX. 4. Distance: 3 mm MIN (From solder joint to case.)

## Lamp wave soldering profile:



#### 4.Cleaning

9

Do not use unspecified chemical liquid to clean LED. They could harm it IF cleaning is necessary, wipe the pin out

## DATASHEET Lamp LED Type ■ Ф3mm LED LAMP A-SA3HR314GGW026-H22



with alcohol. Freon TE or Chlorosen at normal temperature for less than 1 minute or wipe the surface with alcohol.

#### 5.Methods Antistatic Static Electricity

Static electricity is the enemy of lamps emitting blue and green. Workers must put on working rings \( \) gloves clothes hat protect static electricity while working. Wires of the rings keep well together with the floor and there must be wires to connect the irons and the floor.

#### 6. Over-current-proof

- 6-1. Be not over-current.
- 6-2. In order to cooperate LEDs under stable conditions, put protective resisetor in seride. Resistor values can be determined by supplying voltage or current for the LEDs Recommended current is in the range of forward current 5mA-20mA.
- 6-3. Circuit must be designed so that overvoltage is not applied the LED during on/off switching. Transient or pulse current will damage junction of LED die.

#### 7. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $300^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 30W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

#### Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.