


**SURFACE MOUNT FAST RECOVERY RECTIFIERS**

PIN	DESCRIPTION
1	Cathode
2	Anode


**Features**

- ◆ For surface mounted applications
- ◆ Low profile package
- ◆ Glass Passivated Chip Junction
- ◆ Easy to pick and place
- ◆ Fast reverse recovery time
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives

**Mechanical Data**

- ◆ Case: SMB
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 0.098g / 0.003oz

**Absolute Maximum Ratings and Characteristics**

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.


Parameter	Symbols	RS3A	RS3B	RS3D	RS3G	RS3J	RS3K	RS3M	Units			
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V			
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	560	700	V			
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	400	600	800	1000	V			
Maximum Average Forward Rectified Current	$I_{F(AV)}$	3							A			
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	$I_{FSM}$	90							A			
Maximum Forward Voltage at 3 A	$V_F$	1.3							V			
Maximum DC Reverse Current $T_a = 25^\circ\text{C}$ at Rated DC Blocking Voltage $T_a = 125^\circ\text{C}$	$I_R$	5 100							$\mu\text{A}$			
Typical Junction Capacitance at $V_R=4\text{V}$ , $f=1\text{MHz}$	$C_j$	40							pF			
Maximum Reverse Recovery Time <sup>(1)</sup>	$t_{rr}$	150			250	500			ns			
Typical Thermal Resistance <sup>(2)</sup>	$R_{\theta JA}$ $R_{\theta JC}$	48 16							$^\circ\text{C/W}$			
Operating and Storage Temperature Range	$T_j$ , $T_{stg}$	-55 ~ +150							$^\circ\text{C}$			

(1) Measured with  $I_F = 0.5 \text{ A}$ ,  $I_R = 1 \text{ A}$ ,  $I_{rr} = 0.25 \text{ A}$ .


(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.

## SURFACE MOUNT FAST RECOVERY RECTIFIERS


**Fig.1 Maximum Average Forward Current Rating**




**Fig.2 Typical Reverse Characteristics**




**Fig.3 Typical Instantaneous Forward Characteristics**



**Fig.4 Typical Junction Capacitance**



**Fig.5 Maximum Non-Repetitive Peak Forward Surge Current**




## SURFACE MOUNT FAST RECOVERY RECTIFIERS

### PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMB



SMB mechanical data

UNIT	A	E	D	E <sub>1</sub>	A <sub>1</sub>	L	C	b
mm	max	2.44	4.70	3.94	5.59	0.20	1.5	0.305
	min	2.13	4.06	3.3	5.08	0.05	0.8	0.152
mil	max	96	185	155	220	7.9	59	12
	min	84	160	130	200	2.0	32	6

### The recommended mounting pad size

