



Part No	Pin	A	B	C	D	E
WAFER-HY2.0-2PWB	2	2.00	8.00	6.40	4.90	2.50
WAFER-HY2.0-3PWB	3	4.00	10.00	8.40	6.90	3.00
WAFER-HY2.0-4PWB	4	6.00	12.00	10.40	8.90	5.00
WAFER-HY2.0-5PWB	5	8.00	14.00	12.40	10.90	7.00
WAFER-HY2.0-6PWB	6	10.00	16.00	14.40	12.90	9.00
WAFER-HY2.0-7PWB	7	12.00	18.00	16.40	14.90	11.00
WAFER-HY2.0-8PWB	8	14.00	20.00	18.40	16.90	13.00
WAFER-HY2.0-9PWB	9	16.00	22.00	20.40	18.90	15.00
WAFER-HY2.0-10PWB	10	18.00	24.00	22.40	20.90	17.00
WAFER-HY2.0-11PWB	11	20.00	26.00	24.40	22.90	19.00
WAFER-HY2.0-12PWB	12	22.00	28.00	26.40	24.90	21.00
WAFER-HY2.0-13PWB	13	24.00	30.00	28.40	26.90	23.00
WAFER-HY2.0-14PWB	14	26.00	32.00	30.40	28.90	25.00
WAFER-HY2.0-15PWB	15	28.00	34.00	32.40	30.90	27.00
WAFER-HY2.0-16PWB	16	30.00	36.00	34.40	32.90	29.00

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER 2.00 卧贴带扣
			PAR: WAFER-HY2.0-NPWB
DECIMALS: ANGLES:			DWN:
X.:±0.2 X':.±5°			CHKD:
.X:±0.1 X.X':.±3°		APVD:	SCALE1:1 UNIT:MM
.XX:±0.05 X.XX':.±1°		CUSTOMER COPY	SIZE:A4 SHEET:1F1 REV:A