


PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode

DO-214AC/SMA

FEATURES

- ◆ For surface mounted applications
- ◆ Low profile package
- ◆ Glass Passivated Chip Junction
- ◆ Superfast reverse recovery time
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- ◆ Case: SMA
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 0.055g / 0.002oz

Absolute Maximum Ratings and Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single Phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Parameter	Symbols	ES3A	ES3B	ES3C	ES3D	ES3E	ES3G	ES3J	Units				
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	600	V				
Maximum RMS voltage	V_{RMS}	35	70	105	140	210	280	420	V				
Maximum DC Blocking Voltage	V_{DC}	50	100	150	200	300	400	600	V				
Maximum Average Forward Rectified Current at $T_c = 125^\circ C$	$I_{F(AV)}$	3						A					
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I_{FSM}	80						A					
Maximum Forward Voltage at 3 A	V_F	1		1.25		1.68		V					
Maximum DC Reverse Current $T_a = 25^\circ C$ at Rated DC Blocking Voltage $T_a = 125^\circ C$	I_R	5 100						μA					
Typical Junction Capacitance at $V_R=4V$, $f=1MHz$	C_J	40						pF					
Maximum Reverse Recovery Time ⁽¹⁾	t_{rr}	35						ns					
Typical Thermal Resistance ⁽²⁾	$R_{\theta JA}$ $R_{\theta JC}$	50 16						°C/W					
Operating and Storage Temperature Range	T_j , T_{stg}	-55 ~ +150						°C					

(1) Measured with $I_F = 0.5 A$, $I_R = 1 A$, $I_{rr} = 0.25 A$.

(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.

Typical Characteristics

Fig.1 Reverse Recovery Time Characteristic And Test Circuit Diagram





Fig.2 Maximum Average Forward Current Rating




Fig.4 Typical Forward Characteristics




Fig.6 Maximum Non-Repetitive Peak Forward Surge Current




Fig.3 Typical Reverse Characteristics




Fig.5 Typical Junction Capacitance






Fig.7- Typical Transient Thermal Impedance



PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMA



The recommended mounting pad size

