

SPECIFICATION



Customer :

		Receipt
Item:	Crystal Unit	
-		
Туре:	NX3225GD	
Nominal Frequency:	8.000 MHz	
Customer's Spec. No.:		
NDK Spec. No.:	STD-CRA-3	

			Revision Record			
Rev.	Date	Items	Contents	Approved	Checked	Drawn
	28. Feb. 2017	Issue		M.Sato		K.Nakashima

1. Customer's Spec. No.

2. NDK Spec. No. : STD-CRA-3

:

- 3. Type : NX3225GD
- 4. Electrical Specifications

	Paramotors	SVM	E	Electri	cal Sp	ec.	Notes
	Falameters	51101.	min	typ	max	Units	NOLES
1	Nominal frequency	f _{nom}		8.000	-	MHz	
2	Overtone order	-	Fu	ndame	ntal	-	AT-CUT
3	Frequency tolerance	-	-50	-	+50	×10 ⁻⁶	at +25°C
4	Frequency versus temperature characteristics	-	-150	-	+150	×10 ⁻⁶	at -40~+150°C The reference temperature shall be +25°C
5	Equivalent series resistance	-	-	-	500	Ω	IEC π-Network
6	Load capacitance	CL	-	8	-	pF	IEC π-Network
7	Level of drive	-	-	10	200	μW	
8	Insulation resistance	-	500	-	-	MΩ	When terminal to terminal at DC100V ±15V.
9	Operating temperature range	T _{opr}	-40	-	+150	°C	
10	Storage temperature range	T _{str}	-40	-	+150	°C	
11	Air-tightness	-	-	-	3.0×10 ⁻⁹	Pa m ³ /s	Helium leak detector

5. Examination results document

The examination results document is submitted every shipment lot.

6. Application drawing

6.1 External dimension	: EXD14B-00474
6.2 Taping and reel figure	: EXK17B-00247
6.3 Holder marking	: EXH11B-00392
6.4 Reliability assurance Item	: EXS30B-00396
6.5 Recommendation reflow profile	: EXS30B-00344

7. Notice

- 7.1 Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.
- 7.2. Crystal units will be damaged by ultrasonic welding process due to resonance of crystal wafer itself. NDK does not recommend using ultrasonic welding. If Ultra Sonic welding used, NDK strongly recommend verifying crystal unit damage by ultrasonic weld.
- 7.3 Unless we receive request for modification within 3 weeks from the issue date of this NDK specification sheet, we will supply products according to this specification. Also, if you'd like to modify specification of order, which has been placed with delivery request within 3 weeks from the issue data of this specification sheet, we would like to discuss with you separately.
- 7.4 In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.
- 7.5 Where any change to the process condition is made due to the change(s) in the production line, inform personnel of the specifications.
- 7.6 Should this specification data give rise to any disputes relating to any intellectual property rights or any other rights of a third person, the company shall not indemnify anyone for any damage. Their disclosure must not be construed as the grant of a license to use any of the intellectual property rights owned by the company.
- 7.7 If you intend to use products listed on this specification for applications that may result in loss of life or assets (controls relating to safety, medical equipment, aeronautical equipment, space equipment, etc.), please do not fail to advise us of your intention beforehand.
- 7.8 In the company's production process whatever amount of ozone depleting substances (ODS) as specified in the Montreal protocol is not used.
- 7.9 Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.
- 7.10. The appearance color has a different case by purchasing it more than 2 suppliers of the component, but characteristic and reliability are guaranteed
- 7.11. In case of the product long time keep at high temperature and humidity, may affect product characteristic (solder ability) and a packing condition.

Please keep at storage condition of temperature +5°C ~+35°C, humidity ~85%RH.

8. Prohibited items

Be sure to use the product under the following conditions. Otherwise, the characteristics deterioration or destruction of the product may result.

- (1) Reflow soldering heat resistance Peak temperature: 265°C, 10 sec Heating: 230°C or higher, 40 sec Preheating: 150°C to 180°C, 120 sec Reflow passage times: twice
- (2) Manual soldering heat resistance

Pressing a soldering iron of 400°C on the terminal electrode for four seconds (twice).

When using a soldering iron, press its tip on the part below the sealed part, avoiding the glass-sealed part (otherwise, the glass will melt and air-tightness may be lost)



Da	te of Revise	Charge	Approved	Reason				
B 8	.Jan.2013	N.Yamamoto	M.Kubota	Add platin	Add plating thickness			
	Date	Name	Third Angle Projection		Tolerance	Sc	ale	
Drawn	13.May.2010	R.Shariman	Dimension:mm			1 /	15	
Designed	13.May.2010	R.Shariman	Title		Drawing No.		Rev.	
Checked	13.May.2010	K.Komada	NX3225GD		EVD4	4D 00474	D	
Approved	13.May.2010	K.Ueki	Dimension	Drawing	g EXD1	40-004/4	В	

NIHON DEMPA KOGYO CO., LTD.



te of Revise	Charge	Approved	Reason				
6 Mar. 2013	T. Shimizu	K. Oguri The appearanc		earance	ice of a drawing was corrected.		
Date	Name	Third Angle Projection		То	olerance	Sc	ale
30.Jun.2006	H.Yagishita	Dimension:mm				/ -	
30.Jun.2006	H.Yagishita	Title			Drawing No.		Rev.
30.Jun.2006	K.Kubota	NX3225 Series Taping and Reel Spec.			EXK17B-00247		р
30.Jun.2006	T.Ishii			ec.			В
	Ite of Revise 3 Mar. 2013 Date 30.Jun.2006 30.Jun.2006 30.Jun.2006 30.Jun.2006 30.Jun.2006	Ite of Revise Charge 3 Mar. 2013 T. Shimizu Date Name 30.Jun.2006 H.Yagishita 30.Jun.2006 K.Kubota 30.Jun.2006 T.Ishii	Ite of Revise Charge Approved 3 Mar. 2013 T. Shimizu K. Oguri Date Name Third Angle Proje 30.Jun.2006 H.Yagishita Dimension:mr 30.Jun.2006 H.Yagishita Title 30.Jun.2006 K.Kubota NX3225 \$ 30.Jun.2006 T.Ishii Taping and F	Ite of Revise Charge Approved Reason 3 Mar. 2013 T. Shimizu K. Oguri The approved 3 Mar. 2013 T. Shimizu K. Oguri The approved Date Name Third Angle Projection 30.Jun.2006 H.Yagishita Dimension:mm 30.Jun.2006 H.Yagishita Title 30.Jun.2006 K.Kubota NX3225 Series 30.Jun.2006 T.Ishii Taping and Reel Sp	ite of Revise Charge Approved Reason 3 Mar. 2013 T. Shimizu K. Oguri The appearance 3 Mar. 2013 T. Shimizu K. Oguri The appearance Date Name Third Angle Projection To 30.Jun.2006 H.Yagishita Dimension:mm Title 30.Jun.2006 K.Kubota NX3225 Series Taping and Reel Spec. 30.Jun.2006 T.Ishii Taping and Reel Spec. Taping and Reel Spec.	Ite of Revise Charge Approved Reason 3 Mar. 2013 T. Shimizu K. Oguri The appearance of a drawing w 3 Mar. 2013 T. Shimizu K. Oguri The appearance of a drawing w Date Name Third Angle Projection Tolerance 30.Jun.2006 H.Yagishita Dimension:mm 30.Jun.2006 H.Yagishita Title Drawing No. 30.Jun.2006 K.Kubota NX3225 Series EXK17B- 30.Jun.2006 T.Ishii Taping and Reel Spec. EXK17B-	Ite of Revise Charge Approved Reason 3 Mar. 2013 T. Shimizu K. Oguri The appearance of a drawing was corrected 3 Mar. 2013 T. Shimizu K. Oguri The appearance of a drawing was corrected Date Name Third Angle Projection Tolerance Sc 30.Jun.2006 H.Yagishita Dimension:mm 30.Jun.2006 H.Yagishita Title Drawing No. 30.Jun.2006 K.Kubota NX3225 Series Drawing No. 30.Jun.2006 T.Ishii Taping and Reel Spec. EXK17B-00247

NIHON DEMPA KOGYO CO., LTD.



NOTE 1. Frequency Code

Marking Frequency is consist of five digits, first five digits of Nominal Frequency

Example

Nominal Frequency	28.636363 MHz
Frequency Code	28.636

2. Month Code Table

Month	1	2	3	4	5	6	7	8	9	10	11	12
	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Month Code	1	2	3	4	5	6	7	8	9	х	Y	Z

3. Marking contents

Example

Administrative symbol S

*Marking digits are not include a decimal point and dot mark.

	Date of Revise	Charge	Approved	Reason			
	Date	Name	Third Angle Projection		Tolerance	Sc	ale
Drawn	19.May.2008	R.Shariman	Dimension:mm				/
Designe	d 19.May.2008	R.Shariman	Title		Drawing No.		Rev.
Checked	19.May.2008	M.Harada	Crystal Holder Marking			00202	
Approve	d 19.May.2008	K.Kubota			g EXHIIB	EXH110-00392	

NIHON DEMPA KOGYO CO., LTD.

			(page: 1/2)
No.	Test item	Test methods	Spec. code
1	Drop	Devices are dropped from the height 75 cm onto iron plate. Execution 3 times random drops.	А
2	Shock	Acceleration: 49000 m/s ² Duration: 0.15 ms Half-Sine pulse 1 Shocks in 6 mutually perpendicular planes, Total 6 shocks	A
3	Vibration	Frequency range: 10 to 2000 Hz Amplitude or Acceleration: 1.52 mm or 196 m/s^2 Sweep time: 20 min Test time: 4 h×3	A
4	Electrode adherent strength	See remark (1)	В
5	Solderability	Pre-heat temperature: 150 °CPre-heat Time: $60 \sim 120 \text{ s}$ Peak temperature: $240 \pm 5 °C$ 215 °C Over time: $10 \sim 30 \text{ s}$	С
6	Resistance to soldering heat	Pre-heat temperature: 150 °CPre-heat time: $60 \sim 120 \text{ s}$ Test temperature: $260 \pm 5 °C$ Test time: $10 \pm 1 \text{ s}$	A,B
7	Resistance to cold	Leave at -40 \pm 2 °C for 1000 h	A
8	Resistance to heat	Leave at +150±2 °C for 1000 h	A
9	Humidity	Device are left in temperature at +85 \pm 2 °C with relative humidity of 80~85 % for 1000 h	A,D
10	Thermal shock	Device are left into the following temperature cycle as shown in (Figure 1) for 1000 consecutive cycle. $150\pm5 \ ^{\circ}C$ $-40\pm5 \ ^{\circ}C$ $-40\pm5 \ ^{\circ}C$ $-60\pm5 \ ^{\circ}C$ -60 ± 5	A,B

Reliability assurance item

	(page: 2/2)
Spec. code	Specification
А	Frequency tolerance and series resistance should be cleared.
В	After testing unless cracking of materials view of eyes and unless break of seal.
С	The leads shall acquire a new solder coat cover at 90 % of immersed area.
D	Insulation resistance shall be greater than 500 ${\rm M}\Omega$

Reliability assurance item

Remark (1) Electrode adherent strength.

1) Test method condition

Using the solder, soldering Iron or reflow soldering bath shall be used for soldering on test fixture (Glass fiber epoxy laminate : Thickness 1.6mm+/-0.2mm) shown below.



Glass fiber epoxy laminate

2) Specified value

No peel of electrode, no crack, no other abnormality

Recommendation reflow condition



1.IR reflow condition