Shielded Drum Core Inductor

PA4330.XXXNLT Series







- Height: 1.0mm Max
- Footprint: 2.2mm x 1.8mm Max
- Current Rating: up to 3.1A
- Inductance Range: 0.47uH to 2.2uH
- Shielded magnetic circuit reduces leakage flux, Fe base metal core enables high saturation and metalized core termination results in excellent shock resistance

Electrical Specifications @ 25°C — Operating Temperature -40°C to 125°C											
	INDUCTANCE 1MHz, 1V	RATED CURRENT	MIN. SELF-RESONANT FREQUENCY	-	IC STANCE	SATURATION CURRENT	HEATING CURRENT				
PART NUMBER				MAX.	TYP.	(20°C)	20°C Rise	40°C Rise			
	uH +/-20%	A	MHz	mΩ	mΩ	A	A	A			
PA4330.471NLT	0.47	3.1	102	49	41	3.8	2.7	3.1			
PA4330.681NLT	0.68	2.8	77	65	57	3.5	2.5	2.8			
PA4330.102NLT	1	2.35	70	90	75	3.35	2.05	2.35			
PA4330.222NLT	2.2	1.7	39	170	142	1.8	1.45	1.7			


NOTES:

- 1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- 2. The rated current as listed is either the saturation current (20°C) or the heating current (40°C Rise) depending on which value is lower.
- The saturation current is the current at which the initial inductance drops approximately 30% at the stated ambient temperature. This current is determined by placing the component in the specified

ambient environment and applying a short duration pulse current (to eliminate self-heating effect) to the component.

4. The heating current is the DC current required to raise the component temperature by approximately 20°C or 40°C. Take note that the components' performance varies depending on the system conditions. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.

5. Maximum voltage across terminals to be limited to <25Vdc.





Shielded Drum Core Inductor


PA4330.XXXNLT Series



TAPE & REEL INFO









SURFACE MOUNTING TYPE, REEL/TAPE LIST														
ТҮРЕ	REEL SIZE (mm)			TAPE SIZE (mm)									QTY	
	A	В	G	N	E	F	Do	P	Po	P2	W	T	Ko	PCS/REEL
PA4330.XXXNLT	Ø178	14.4	8.4	58	1.75	3.5	1.5	4	4	2	8	0.25	1.2	2000

Typical Performance Curves



Shielded Drum Core Inductor

PA4330.XXXNLT Series



For More Information:

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

3

PulseElectronics.com

P749.D (12/23)

