
# JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

## AD-BCX54/55/56\* series Plastic-Encapsulated Transistor

AD-BCX54/55/56\* series Transistor (NPN)

#### **FEATURES**

- High collector current
- Low collector-emitter saturation voltage
- Complementary types: AD-BCX51/52/53\* series (PNP)
- AEC-Q101 qualified



## MAXIMUM RATINGS (T<sub>j</sub> = 25°C unless otherwise specified)

Parameter	Symbol	AD-BCX54*	AD-BCX55*	AD-BCX56*	Unit
Collector-base voltage	V <sub>CBO</sub>	45	60	100	V
Collector-emitter voltage	V <sub>CEO</sub>	45	60	80	V
Emitter-base voltage	V <sub>EBO</sub>		5		V
Collector continuous current	lc		1		А
Peak pulsed collector current	Ісм	2			А
Base continuous current	lв	100			mA
Peak pulsed base current ( $t_p < 1ms$ )	I <sub>BM</sub>	200			mA
Collector power dissipation	Pc <sup>1)</sup>	0.5			W
Thermal resistance from junction to ambient	R <sub>0JA</sub> <sup>1)</sup>	250			°C/W
Collector power dissipation	Pc <sup>2)</sup>	2			W
Thermal resistance from junction to ambient	R <sub>0JA</sub> <sup>2)</sup>	61.5			°C/W
Operating junction and storage temperature range	T <sub>j,</sub> T <sub>stg</sub>	-55 ~ 150			°C

#### ELECTRICAL CHARACTERISTICS (T<sub>j</sub> = 25°C unless otherwise specified)


Paramete	Parameter		Test condition	Min	Тур	Max	Unit
	AD-BCX54*			45	-	-	
Collector-base breakdown voltage	AD-BCX55*	V <sub>(BR)CBO</sub>	$I_{C} = 0.1 \text{mA}, I_{E} = 0 \text{A}$	60	-	-	V
	AD-BCX56*			100	-	-	
	AD-BCX54*			45	-	-	v
Collector-emitter breakdown voltage	AD-BCX55*	V <sub>(BR)CEO</sub> <sup>3)</sup>	$I_{\rm C} = 10 {\rm mA}, I_{\rm B} = 0 {\rm A}$	60	-	-	
	AD-BCX56*			80	-	-	
Base-emitter breakdow	n voltage	V <sub>(BR)EBO</sub>	$I_E = 10 \mu A, I_C = 0A$	5	-	-	V
Collector-base cut-off c	urrent	I <sub>CBO</sub>	$V_{CB} = 30V, I_{E} = 0A$	-	-	100	nA
Emitter-base cut-off cur	rent	I <sub>EBO</sub>	$V_{EB} = 5V, I_{C} = 0A$	-	-	100	nA
			V <sub>CE</sub> = 2V, I <sub>C</sub> = 5mA	40	-	-	
DC current gain		h <sub>FE(2)</sub> 3)	V <sub>CE</sub> = 2V, I <sub>C</sub> = 150mA	63	-	250	-
		h <sub>FE(3)</sub> 3)	V <sub>CE</sub> = 2V, I <sub>C</sub> = 500mA	25	-	-	
Collector-emitter saturation voltage		V <sub>CE(sat)</sub> <sup>3)</sup>	I <sub>C</sub> = 500mA, I <sub>B</sub> = 50mA	-	-	0.5	V
Base-emitter voltage		V <sub>BE</sub> <sup>3)</sup>	I <sub>C</sub> = 500mA, V <sub>CE</sub> = 2V	-	-	1	V
Transition frequency		f⊤	V <sub>CE</sub> = 5V, I <sub>C</sub> = 10mA, f = 100MHz	-	130	-	MHz

## CLASSIFICATION OF h<sub>FE(2)</sub>


RANK	AD-BCX54-10, AD-BCX55-10,	AD-BCX54-16, AD-BCX55-16,
	AD-BCX56-10	AD-BCX56-16
RANGE	63 ~ 160	100 ~ 250
MARKING	BC, BG, BK	BD, BM, BL


1) Measured with the device mounted on 1cm×1cm×0.8mm FR-4 board with no copper, in a still air environment with  $T_a$  = 25 °C.

2) Measured with the device mounted on 2.54 cm $\times 2.54$  cm $\times 1.6$  mm FR-4 board with double sided 1oz copper, in a still air environment with T<sub>a</sub> = 25°C. 3) Pulse test.




#### SOT-89-3L PACKAGE OUTLINE DIMENSIONS





Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min	Max	Min	Max	
A	1.400	1.600	0.055	0.063	
b	0.320	0.520	0.013	0.020	
b1	0.400	0.580	0.016	0.023	
С	0.350	0.440	0.014	0.017	
D	4.400	4.600	0.173	0.181	
D1	1.550	REF.	0.061 REF.		
E	2.300	2.600	0.091	0.102	
E1	3.940	4.250	0.155	0.167	
е	1.500 TYP.		0.060 TYP.		
e1	3.000 TYP.		0.118	TYP.	
L	0.900	1.200	0.035	0.047	

### SOT-89-3L SUGGESTED PAD LAYOUT




Note:

- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

#### SOT-89-3L TAPE AND REEL


#### SOT-89-3L Embossed Carrier Tape




Packaging Description: SOT-89-3L parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 1,000 units per 7" or 18.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

				Dimensions a	are in millime	ter				
Pkg type	А	В	С	d	E	F	P0	Р	P1	W
SOT-89-3L	4,85	4,45	1,85	Ø1.50	1,75	5,50	4,00	8,00	2,00	12,00

#### SOT-89-3L Tape Leader and Trailer



SOT-89-3L Reel



Dimensions are in millimeter									
Reel Option	D	D1	D2	G	Н	Γ	W1	W2	
7"Dia	Ø180.00	60.00	R32.00	R86.50	R30.00	Ø13.00	13.20	16.50	

REEL	Reel Size	Box	Box Slze(mm)	Carton	Carton Slze(mm)	G.W.(kg)
1000 pcs	7 inch	10,000 pcs	203×203×195	40,000 pcs	438×438×220	

#### JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD. 13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

#### LEGAL DISCLAIMER

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### INFORMATION

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (<u>www.jscj-elec.com</u>).

#### WARNINGS

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.