

2520

[2.5×2.0×0.55 mm]

3225

[3.2×2.5×0.70 mm]



Surface Mount Crystals


Fundamental

Frequency Range

8MHz~125MHz

Features

- Small size SMD crystal units with 2.5×2.0 (2520), 3.2×2.5 (3225), seam sealed package or glass sealed package.
- The entire package can be grounded via the top metal lid and the bottom pads
- Small footprint. Ideal for space constrained applications
- Exhibits extremely low aging with a high shock & vibration resistance
- Applications: Mobile phone, WI-LAN, Wireless communications, Bluetooth, Clock for MPU, Radio communications, etc.



Standard Specifications

Item / Type	2520	3225
Frequency Range	12~54 MHz (Fund.)	8~125 MHz(Fund.)
Load Capacitance	8pF~32pF, or specify	
Drive Level	100 μW typical	
Frequency Tolerance (at 25°C)	± 10ppm, ±20ppm or ±30ppm (max.)	
Aging	±3ppm / Year (max.)	
Storage Temperature Range	-55°C~+125°C	

ESR (Equivalent Series Resistance)

2520		3225	
Frequency Range	E.S.R	Frequency Range	E.S.R
12~15.999MHz	150 Ω max.	8~9.9999 MHz	250 Ω max.
16~29.999MHz	100 Ω max.	10~11.999 MHz	200 Ω max.
30~54MHz	70 Ω max.	12~29.999 MHz	80 Ω max.
		30~125 MHz	40 Ω max.

Frequency stability Vs Operating temperature range

Temp. (°C)	ppm					
	±5	±10	±15	±20	±25	±30
-10~+60	▲	○	○	○	○	○
-20~+70	×	○	○	○	○	○
-40~+85	×	×	○	○	○	○

▲: Conditional
○: Available
×: Not available

2520

[2.5×2.0×0.55 mm]

3225

[3.2×2.5×0.70 mm]



Surface Mount Crystals





Fundamental

Frequency Range

8MHz~125MHz

Outline Dimensions (Unit: mm)

2520 (2.5×2.0×0.55 mm)



3225 (3.2×2.5×0.70 mm)

