# **SMT Power Inductors**

Unshielded Drum Core - P0762NL Series









Height: 3.0mm Max

**(***e***) Footprint:** 13.0mm x 9.4mm Max

@ Current Rating: up to 2.0A

Inductance Range: 10μH to 1000μH

Electrical Specifications @ 25°C - Operating Temperature -40°C to +130°C					
Part <sup>6,7</sup> Number	Inductance @ Ipx Abc (µH ± 20%)	Irated <sup>5</sup> (A)	DCR (MAX) (mΩ)	Saturation Current (A) @ 25°C	Heating Current (A)
P0762.103NL	10	2.0	110	2.4	2.0
P0762.153NL	15	1.5	150	2.0	1.5
P0762.223NL *	22	1.3	230	1.6	1.3
P0762.333NL *	33	1.1	300	1.4	1.1
P0762.473NL*	47	0.8	390	1.0	0.8
P0762.683NL	68	0.7	660	0.9	0.7
P0762.104NL	100	0.6	840	0.7	0.6
P0762.154NL	150	0.5	1200	0.6	0.5
P0762.224NL	220	0.4	1900	0.5	0.4
P0762.334NL*	330	0.3	2700	0.4	0.3
P0762.474NL*	470	0.2	4000	0.3	0.2
P0762.684NL	680	0.1	5300	0.2	0.1
P0762.105NL *	1000	0.05	8400	0.1	.05


### Notes:


- 1. The temperature of the component (ambient plus temperature rise) must be within the specified operating temperature range.
- 2. Inductance tested at 100kHz, 10mV<sub>RMS</sub>
- 3. Inductance drop = 10% typical at the Saturation Current
- 4. ΔT = 15°C rise typical at the Heating Current
- 5. The rated current is the lower of the saturation or heating current
- 6. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. P0762.103NL becomes P0762.103NLT). Pulse complies to industry standard tape and reel specification EIA481.
- 7. The "NL" suffix indicates an RoHS-compliant part number. Non-NL suffixed parts are not necessarily RoHS compliant, but are electrically and mechanically equivalent to NL versions. If a part number does not have the "NL" suffix, but an RoHS compliant version is required, please contact Pulse for availability.
- \* Contact Pulse for availability

## **Mechanical**

## Schemati

### P0762.XXXNL





**Dimensions:**  $\frac{Inches}{mm}$ 

Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0.25}$ 

# SMT Power Inductors Unshielded Drum Core - P0762NL Series

### For More Information:

Americas - prodinfo\_power@pulseelectronics.com | Europe - power-apps-europe@pulseelectronics.com | Asia - power-apps-asia@pulseelectronics.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2021. Pulse Electronics, Inc. All rights reserved.

