


## 15Amp Surface Mount Schottky Barrier Rectifiers





## SB1545L

**Features:**

- High current capacity, low forward voltage.
- Excellent high temperature stability.
- High forward surge capacity.
- RoHS compliant, and Halogen free.

TO-277





**Absolute Maximum Ratings** (Ta=25°C unless otherwise noted)

Characteristic	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Recurrent Peak Reverse Voltage	$V_{RRM}$	$I_R=0.5mA$	45	-	-	V
Average Forward Current	$I_{F(AV)}$	$V_R=45V@T_j=25^\circ C$	-	-	15	A
Peak Forward Surge Current, 8.3ms single half sine-wave	$I_{FSM}$	$V_R=45V@T_j=25^\circ C$	-	-	200	A
Forward Voltage(Note1)	$V_F$	$I_F=15A$	-	-	0.55	V
		$I_F=15A@100^\circ C$	-	0.50	-	
Reverse Leakage Current(Note1)	$I_R$	$V_R=45V@T_j=25^\circ C$	-	-	0.2	mA
		$V_R=45V@T_j=100^\circ C$	-	-	20	
Operating Junction Temperature	$T_j$	-	-	-	150	°C
Storage Temperature Range	$T_{stg}$	-	-40	-	150	
Thermal Resistance(Note2)	$R_{th(JA)}$	-	-	31	-	°C/W

Note 1: Pulse test width PW=300usec. 1%duty cycle

Note 2: Polymide PCB, 2oz. copper. Cathode pad dimensions 18.8\*14.4mm. Anode pad dimensions 5.6\*14.1mm

15Amp Surface Mount Schottky Barrier Rectifiers

Typical Characteristics

RATING AND CHARACTERISTIC CURVES

FIG. 1- FORWARD CURRENT DERATING CURVE




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS





FIG. 4-TYPICAL REVERSE CHARACTERISTICS





15Amp Surface Mount Schottky Barrier Rectifiers

Package Dimension

TO-277

Units: mm



NO	Dimensions	NO	Dimensions
A	1.20±0.1	e	1.84Typ
A2	0.25±0.05	E1	5.3±0.1
b1	0.9±0.1	E2	3.3±0.2
b2	1.8±0.1	L	0.6±0.1
D	3.95±0.1	L1	0.6±0.1
D2	3.00Typ	W	1.3±0.2
E	6.5±0.1	W1	0.8±0.15
<b>All Dimensions in mm</b>			