

1-Line Bidirectional ESD Protection Diode

General description

Low capacitance bidirectional ElectroStatic Discharge (ESD) protection diode in a DFN1006(SOD882) leadless ultra small Surface-Mounted Device (SMD) plastic package designed to protect one signal line from the damage caused by ESD and other transients.

Features and benefits

- Femtofarad capacitance: $C_j = 8\text{pF}$ (Typ)
- Ultra Low Leakage: nA Level
- Low clamping voltage $V_c = 21\text{ V}$
- IEC 61000-4-2:
Air discharge: $\pm 15\text{KV}$, Contact discharge: $\pm 30\text{KV}$
- IEC 61000-4-5 (8/20 μs): $I_{PPM} = 8.0\text{ A}$
- RoHS Compliant



Application information

- Cellular Handsets and Accessories
- Keypads, Side Keys, LCD Displays
- Notebooks and Handhelds
- Personal Digital Assistants
- Portable Instrumentation
- Digital Cameras
- Audio Players
- Peripherals

Ordering information

Device	Package	Marking	Packaging
ESD8D12C	DFN1006-2L	AA	10000/Tape & Reel

Schematic & Pin configuration



Simplified outline	Graphic symbol
	

Maximum Ratings ($T_{OP} = 25^\circ C$, unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power ($T_p = 8/20 \mu s$)	P_{PPM}	136	W
Rated Peak Pulse Current ($T_p = 8/20 \mu s$)	I_{PPM}	8.0	A
Maximum lead temperature for soldering during 10s	T_L	260	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C
Operating Temperature Range	T_{OP}	-40 to +125	°C
Maximum junction temperature	T_j	150	°C
ESD voltage IEC 61000-4-2 (air discharge)	V_{ESD}	30	kV
ESD voltage IEC 61000-4-2 (contact discharge)	V_{ESD}	30	kV


Electrical Characteristics ($T_{OP} = 25^\circ C$, unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Condition
Reverse Working Voltage	V_{RWM}	--	--	12.0	V	
Breakdown Voltage	V_{BR}	13.0	--	15.5	V	$I=1mA$
Leakage Current I_{LEAK}	I_R	--	--	200	nA	$V_{RWM}=12V$
Clamping Voltage	V_C	--	--	17.0	V	$I_P=8.0A, T_p=8/20\mu s$
Junction Capacitance	C_J	--	8	12	pF	$V_R=0V, f=1MHz$

Typical Electrical and Thermal Characteristics (Curves)


Package Outline Dimensions

DFN1006-2L



DFN1006-2L (mm)

Dim	Min	Typ.	Max
A	0.45	0.50	0.55
A1	0	0.02	0.05
b	0.45	0.5	0.55
c	0.1	0.15	0.18
D	0.95	1.00	1.05
E	0.55	0.60	0.65
L	0.20	0.25	0.30
L1	0.035	0.05	0.065