

## 0.1-3.8GHz SP8T Diversity Switch

#### **Features**

- Broadband frequency range: 0.1 to 3.8 GHz
- Low insertion loss: 0.85dB typical @ 3.8 GHz
- High isolation: >16dB @ 3.8 GHz
- Integrated logic
- Small QFN 2mmX2mmX0.55mm-14L package

### **Applications**

- 2G/3G/4G antenna diversity and primary
- Cellular modems, tablets and USB Devices
- Other RF front-end modules

### **General Description**

The AW13418RQNR is a SP8T switch with low insertion loss and high Isolation. It can be used to support band switching and mode switching in antenna diversity systems for 2G/3G/4G, data cards and tablets.

The symmetrical design of internal ports makes it convenient for PCB routing and adjustment of receiving and transmitting signals. The band/mode switching is realized by the GPIO pins as referenced in the chip block diagram and the control logic.

The AW13418RQNR is provided in a compact QFN 2mmX2mmX0.55mm-14L.

# **Typical Application Circuit**




Figure 1 Typical Application Circuit of AW13418RQNR

All trademarks are the property of their respective owners.



## **Pin Configuration And Top Mark**




Figure 2 Pin Configuration and Top Mark

### **Pin Definition**

No.	NAME	DESCRIPTION
1	RF5	RF I/O path 5
2	RF3	RF I/O path 3
3	RF1	RF I/O path 1
4	VDD	DC power supply
5	V3	DC control voltage 3
6	V2	DC control voltage 2
7	V1	DC control voltage 1
8	NC	Not connected
9	RF2	RF I/O path 2
10	RF4	RF I/O path 4
11	RF6	RF I/O path 6
12	RF8	RF I/O path 8
13	ANT	Antenna port
14	RF7	RF I/O path 7

Note: Bottom ground paddles must be connected to ground.



# **Functional Block Diagram**





Figure 3 Functional Block Diagram

# **Ordering Information**

Part Number	Temperature	Package	Marking	Moisture Sensitivity Level	Environmental Information	Delivery Form
AW13418RQNR	-40°C~85°C	QFN 2mmX2mm X0.55mm- 14L	4E5C	MSL1	ROHS+HF	3000 units/ Tape and Reel





# **Absolute Maximum Ratings**(NOTE1)

PARAMETER	PARAMETERS					
Supply Voltage Ran	Supply Voltage Range VDD					
Control Voltage Range	Control Voltage Range V1,V2,V3					
RF input power(RF1	RF input power(RF1 to RF8)					
Operating Free-air Tempe	Operating Free-air Temperature Range					
Storage Temperatur	-65°C to 150°C					
Lead Temperature (Solderi	260°C					
	+, 4/7					
HBM (NOTE 2)	±2kV					
CDM (NOTE 3)		±1kV				

NOTE1: Conditions out of those ranges listed in "absolute maximum ratings" may cause permanent damages to the device. In spite of the limits above, functional operation conditions of the device should within the ranges listed in "recommended operating conditions". Exposure to absolute-maximum-rated conditions for prolonged periods may affect device reliability.

NOTE2: The human body model is a 100pF capacitor discharged through a 1.5k $\Omega$  resistor into each pin. Test method: ESDA/JEDEC JS-001-2017

NOTE3: All pins. Test Condition: ESDA/JEDEC JS-002-2018



### **Electrical Characteristics**

VDD=2.8V, V1=V2=V3=0/1.8V, PIN=0dBm, Temp=+25°C,  $Z_0$ =50 $\Omega$ . (unless otherwise noted)

	PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
DC Speci	fications					
VDD	Supply Voltage		2.4	2.8	3	V
IDD	Supply Current			45	80	μΑ
VCTL_H VCTL_L	Control Voltage High Low		1.35	1.8	3 0.45	V
Ictl	Control Current	VCTL = 1.8V		0.1	1	μΑ
t <sub>ON</sub>	Turn-on Switching Time	50% of final control voltage to 90% of final RF power, switching between RF1/2/3/4/5/6/7/8		0.5	1	μs
RF Specif	fications					
IL	Insertion loss(ANT pin to RF1- RF8)	0.1-1.0GHz 1.0-2.0GHz 2.0-2.7GHz 2.7-3.8GHz		0.31 0.43 0.56 0.85	0.46 0.57 0.73 1.16	dB dB dB dB
ISO	Isolation (ANT pin to RF1-RF8)	0.1-1.0GHz 1.0-2.0GHz 2.0-2.7GHz 2.7-3.8GHz	30 23 20 16	40 30 24 18		dB dB dB dB
RL	Input return loss (ANT pin to RF1-RF8)	0.1-1.0GHz 1.0-2.0GHz 2.0-2.7GHz 2.7-3.8GHz	20 16 12 10	27 22 20 14		dB dB dB dB
2fo	Second harmonics (ANT pin to RF1-RF8)	PIN=+26dBm, 0.1-3.8GHz		90		dBc
3fo	Third harmonics (ANT pin to RF1-RF8)	PIN=+26dBm, 0.1-3.8GHz		75		dBc
P <sub>0.1dB</sub>	0.1dB Compression Point (ANT pin to RF1-RF8)	0.1-3.8GHz		31		dBm



## **Timing Diagram (Power ON and OFF sequence)**

It is very important that the user adheres to the correct power-on/off sequence in order to avoid damaging the device. The control signal V1, V2, V3 should be set to 0V unless VDD is set in the operating voltage range.

#### Power ON:

- 1) Apply voltage supply --- VDD
- 2) Set Controls---V1, V2, V3
- 3) Apply RF input

Change switch position from one RF port to another:

- 1) Remove RF input
- 2) Change control voltages V1, V2, V3 to set the switch to desired RF port
- 3) Apply RF input

#### Power OFF:

- 1) Remove RF input
- 2) Remove control voltages-V1, V2, V3
- 3) Remove VDD input




Figure 4 Power on/Change switch/Power off sequence





# **AW13418RQNR Contral Logic**

C	ontro Pins	ol		Switch RF I/O								
V1	V2	V3	RF1	RF2 RF3 RF4 RF5		RF6	RF7	RF8				
0	0	0	ON	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation		
0	0	1	Isolation	ON	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation		
0	1	0	Isolation	Isolation	ON	Isolation	Isolation	Isolation	Isolation	Isolation		
0	1	1	Isolation	Isolation	Isolation	ON	Isolation	Isolation	Isolation	Isolation		
1	0	0	Isolation	Isolation	Isolation	Isolation	ON	Isolation	Isolation	Isolation		
1	0	1	Isolation	Isolation	Isolation	Isolation	Isolation	ON	Isolation	Isolation		
1	1	0	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation	ON	Isolation		
1	1	1	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation	Isolation	ON		

Aug. 2022 V1.4


## **Tape and Reel Information**





- A0: Dimension designed to accommodate the component width
- B0: Dimension designed to accommodate the component length K0: Dimension designed to accommodate the component thickness
- W: Overall width of the carrier tape
- P0: Pitch between successive cavity centers and sprocket hole
  P1: Pitch between successive cavity centers
- P2: Pitch between sprocket hole D1: Reel Diameter
- D0: Reel Width

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### DIMENSIONS AND PIN1 ORIENTATION


D1	D0	A0	B0	K0	P0	P1	P2	W	Pin1 Quadrant
(mm)	Fill Quadralit								
	8.4							8	Q1


All dimensions are nominal


Figure 5 Tape and Reel



# **Package Description**









Unit: mm

Figure 6 Package Description



### **Land Pattern Data**





Unit: mm **Land Pattern Data** 

Figure 7



# **Revision History**

Vision	Date	Change Record		
V1.0	Aug. 2021	Officially Released		
V1.1	Sep. 2021	Add S Parameter of 3.8 GHz		
V1.2	Oct. 2021 Modify Formats			
V1.3	Aug. 2022	Modify Formats		
V1.4	Aug. 2022	Update Absolute Maximum Ratings		



#### **Disclaimer**

Information in this document is believed to be accurate and reliable. However, Shanghai AWINIC Technology Co., Ltd (AWINIC Technology) does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

AWINIC Technology reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. Customers shall obtain the latest relevant information before placing orders and shall verify that such information is current and complete. This document supersedes and replaces all information supplied prior to the publication hereof.

AWINIC Technology products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an AWINIC Technology product can reasonably be expected to result in personal injury, death or severe property or environmental damage. AWINIC Technology accepts no liability for inclusion and/or use of AWINIC Technology products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications that are described herein for any of these products are for illustrative purposes only. AWINIC Technology makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

All products are sold subject to the general terms and conditions of commercial sale supplied at the time of order acknowledgement.

Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Reproduction of AWINIC information in AWINIC data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. AWINIC is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of AWINIC components or services with statements different from or beyond the parameters stated by AWINIC for that component or service voids all express and any implied warranties for the associated AWINIC component or service and is an unfair and deceptive business practice. AWINIC is not responsible or liable for any such statements.