




Sensors > Pressure Sensors > Board Mount Pressure Sensors



Board Level Pressure Sensor Type: **Digital Pressure and Altimeter Sensor Modules**
Board Level Pressure Sensor Style: **Absolute**
Pressure: **30000 mbar**
Output/Span: **24 bit ADC**
Board Level Pressure Sensor Accuracy: **±400mbar**

Features

Product Type Features

Board Level Pressure Sensor Type	Digital Pressure and Altimeter Sensor Modules
Board Level Pressure Sensor Style	Absolute

Electrical Characteristics

Board Level Pressure Sensor Supply Voltage	1.8 – 3.6 V
--	-------------

Dimensions

Dimensions	6.2 x 6.4 mm[.24 x .25 in]
------------	----------------------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Resolution	.5
Pressure	30000 mbar
Output/Span	24 bit ADC
Board Level Pressure Sensor Accuracy	±400mbar

Packaging Features

Board Level Pressure Sensor Package	Surface Mountable
-------------------------------------	-------------------

Other



Sensor Options	No Option
----------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # MS580314BA01-00
MS5803-14BA01 DIGIT PRESSURE SENSOR TUBE



TE Part # MS580302BA01-00
MS5803-02BA01 DIGIT PRESSURE SENSOR TUBE



TE Part # MS580305BA01-00
MS5803-05BA 5BAR WHITE GEL TUBE



TE Part # MS580301BA01-00
MS5803-01BA01 PRESSURE SENSOR TUBE






TE Part # MS580502BA01-50

MINIATURE DIGITAL PRESSURE
SENSOR

Also in the Series | MEAS MS5803



Board Mount Pressure Sensors(10)

Customers Also Bought



TE Part #188275-8

MICRO-MATCH SMD FTE



TE Part #1-534998-0

20 MODIV VRT DR CE 100/125



TE Part #1-534998-5

30 MODIV VRT DR CE 100/125



TE Part #1-534998-7

34 MODIV VRT DR CE 100/125



TE Part #5-534998-8

16 MODIV VRT DR CE 100/125



TE Part #282006-013

44A0111-16-6

TE Part #4004000070

DSL 1010.01 S1HV 5M

TE Part #4004000346

DSL 1010.02 S1HV

TE Part #4004000444

DSF 2210.00 S3HV



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_MS580330BA01-00_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_MS580330BA01-00_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_MS580330BA01-00_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Data sheet

English