



DEUTSCH | DEUTSCH DT

TE Internal #: DT06-2S-EP04

Housing for Female Terminals, Wire-to-Wire, 2 Position, .215 in [5.46 mm] Centerline, Sealable, Gray, Wire & Cable, Power & Signal, DEUTSCH DT

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DT Plug Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **5.46 mm [ .215 in ]**

Sealable: **Yes**

[All DEUTSCH DT Plug Connectors \(212\)](#)

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

### Configuration Features

Blank Cavity Position	0
Number of Positions	2
Number of Rows	1

### Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

### Body Features

Cable Exit Angle	180°
Primary Product Color	Gray



### Contact Features

Contact Size	Size 16
Contact Type	Socket
Mating Pin Diameter	1.59 mm[.063 in]
Contact Current Rating (Max)	13 A

### Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	PA GF
Centerline (Pitch)	5.46 mm[.215 in]

### Dimensions

Connector Height	15.77 mm[.621 in]
Product Width	15.01 mm[.591 in]
Product Length	31.19 mm[1.228 in]
Compatible Insulation Diameter Range	2.23 – 3.68 mm[.088 – .145 in]

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

Degree of Protection	IP68, IP6K9K
Compatible With Agency/Standards Products	SAE J2030
UL Flammability Rating	12mm Flame Test per Standard UL-94

### Packaging Features

Packaging Quantity	1600
Packaging Method	Box



## Other

Serviceable	Yes
Connector Position Assurance Capable	No

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-J67-DSCC16  
DEUTSCH Size 16 Crimp Contacts



TE Part # CAT-D487-H342  
DEUTSCH DT Headers



TE Part # CAT-D487-W416  
Wedgelocks: DEUTSCH DT



TE Part # DT04-2P-EP04  
REC, 2P, GRY, N, CAP



TE Part # CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part # CAT-D48-SP729  
DEUTSCH Sealing Plugs



TE Part # DT-RT1  
EXT TOOL, FRONT RELEASE



TE Part # 1011-344-0205  
DUST CAP, 2P, PLG, BLK, DT



TE Part # 776363-1  
SEALING PLUG, SZ 16 CAVITY




TE Part # W2S-P070-R  
SEAL RETN WEDGE.RED. DT 2 WAY.




TE Part # W2S-P070-U  
SEAL RETN WEDGE. BLUE.DT 2 WAY



TE Part # W2S-P070-Y  
SEAL RETN WEDGE. ORANGE DT 2 W



TE Part # 1062-14-0177  
SOC, SF, SIZE 16, 14-18, SN/SN



TE Part # DTF13-2PB  
HDR, 2P, BLK, RA, SN/NI/CU, B


Also in the Series | **DEUTSCH DT**




Automotive Connector Caps & Covers  
(19)



Automotive Connector Locks &  
Position Assurance(74)




Automotive Housings(657)




Connector Backshells(58)







Connector Seals & Cavity Plugs(6)



Connector Strain Relief(28)



Insertion & Extraction Tools(3)



Other Automotive Connector Accessories(27)



PCB Headers & Receptacles(103)

## Customers Also Bought



TE Part #HD36-24-33SN  
PLG, 33P, AL, N, 20, S



TE Part #282680-1  
SPLASH PR.ASSY W.SEC.LOCK2W TY



TE Part #6-160449-3  
FF 250 REC 1-2.5MM2 PB SILVER  
PLATED LP



TE Part #2350890-1  
20POS, HYBRID, SOC HSG ASSY, SLD,  
COD A



TE Part #HDP26-24-9SE  
DEUTSCH HDP20 Housings



TE Part #929940-6  
JPT REC 2.8 Contact SWS Ag (LP)



TE Part #2350890-2  
20POS, HYBRID, SOC HSG ASSY, SLD,  
COD B



TE Part #2350890-3  
20POS, HYBRID, SOC HSG ASSY, SLD,  
COD C

## Documents

### Product Drawings

PLG, 2P, GRY, N, CAP

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_DT06-2S-EP04\_B.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_DT06-2S-EP04\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_DT06-2S-EP04\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Engineering Report](#)

English

---

### Agency Approvals

[UL Report](#)

English