



- High reliability and high voltage are realized by hybrid electrolyte
- Endurance with ripple current: 5,000 hours at 105°C
- For high reliability applications.

(Automotive equipment, Base station equipment, etc.)

- RoHS2 Compliant
- OHalogen Free
- AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.

HXA Higher temperature HXB Longer life HXD




SPECIFICATIONS

Items	Characteristics							
Category Temperature Range	-55 to +105℃							
Rated Voltage Range	80V _{dc}							
Capacitance Tolerance	±20% (M)				(at 20℃, 120Hz)			
Leakage Current	I=0.01CV or 3μ A, whichever is greater Where, I: Max. leakage current (μ A), C: Nominal capacitance(μ F), V: Rated voltage(V) (at 20°C after 2 minutes)							
Dissipation Factor	Rated voltage(V _{dc})	80V						
(tan δ)	$tan \delta$ (Max.)	0.08			(at 20℃, 120Hz)			
Low Temperature Characteristics (Max. Impedance Ratio)	$Z(-25^{\circ}C)/Z(+20^{\circ}C)$ ≦1.5 $Z(-55^{\circ}C)/Z(+20^{\circ}C)$ ≦2.0 (at 100kHz)							
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated							
	ripple current is applied (th	ne peak v	oltage shall not exceed the rated	voltage) for 5,000 hours at 105 $^\circ$	C.			
	Capacitance change	≦±30°	% of the initial value					
D.F. $(\tan \delta)$ $\leq 200\%$ of the initial specified value								
	ESR	≤ 200°	% of the initial specified value					
	Leakage current	≦ The	initial specified value					
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105 °C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to item 4.1 of JIS C 5101-4.							
	Capacitance change	≦±30°	% of the initial value					
	D.F. (tan δ)	≦ 2009	% of the initial specified value					
	ESR	≤ 200°	% of the initial specified value					
	Leakage current	≦ The	initial specified value					

◆DIMENSIONS [mm]


• Terminal Code : A

• Size code : HA0 and JA0



Terminal Code : G(Vibration resistant structure)


• Size code : HA0 and JA0



Size Code	φD	L	Α	В	С	W	Р
HA0	8	10.0	8.3	8.3	9.0	0.7 to 1.1	3.1
JA0	10	10.0	10.3	10.3	11.0	0.7 to 1.1	4.5

: Dummy terminals

◆PART NUMBERING SYSTEM



Please refer to "Product code guide (conductive polymer hybrid type)"

◆MARKING



Rated voltage symbol

Rated voltage (Vdc)	Symbol		
80	К		





STANDARD RATINGS

	WV (V _{dc})	Cap (μF)	Size code	ESR (mΩmax./20°C, 100kHz)	Rated ripple current (mArms/105℃, 100kHz)	Part No.	
Г	00	22	HA0	45	1,600	HHXB800□RA220MHA0G	
80	39	JA0	35	1,700	HHXB800□RA390MJA0G		

 $[\]square$: Enter the appropriate terminal code.

♦RATED RIPPLE CURRENT MULTIPLIERS

Frequency Multipliers

Capacitance(µF) Frequency(Hz)	120	1k	5k	10k	20k	30k	100k to 500k
22	0.07	0.30	0.50	0.60	0.70	0.75	1.00
39	0.10	0.40	0.60	0.70	0.80	0.80	1.00