

**TO-252-2L Plastic-Encapsulate MOSFETS****CJU50SN10 N-Channel Power MOSFET**


$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	16.5mΩ@10V	50A

DESCRIPTION

The CJU50SN10 uses shielded gate trench technology and design to provide excellent $R_{DS(ON)}$ with low gate charge. It can be used in a wide variety of applications

TO-252-2L


1. GATE
2. DRAIN
3. SOURCE

**FEATURES**


- High Power and current handing capability
- Load switch
- High density cell design for ultra low $R_{DS(ON)}$
- Lead free product is acquired
- Good stability and uniformity with high E_{AS}
- Excellent package for good heat dissipation

APPLICATIONS

- SMPS and general purpose applications
- Hard switched and high frequency circuits
- Uninterruptible Power Supply
- Power management

MARKING

U50SN10= Device code
Solid dot = Green molding compound device,
if none, the normal device
XXXX=Code

EQUIVALENT CIRCUIT**ABSOLUTE MAXIMUM RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)**

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	±20	
Continuous Drain Current	I_D	50	A
Pulsed Drain Current ⁽¹⁾	I_{DM}	170	
Maximum Power Dissipation ⁽⁴⁾	P_D	50	W
Avalanche energy*	E_{AS}	80	mJ
Thermal Resistance from Junction to Case	$R_{\theta JC}$	2.5	°C/W
Thermal Resistance from Junction to Ambient ⁽³⁾	$R_{\theta JA}$	62	°C/W
Junction Temperature	T_J	150	°C
Storage Temperature	T_{STG}	-55~ +150	

* EAS test condition $V_{DD}=50V$, $R_G=25\ \Omega$, $L=0.3\ \text{mH}$, starting $T_J=25\ ^\circ\text{C}$.

MOSFET ELECTRICAL CHARACTERISTICS







$T_a=25\text{ }^\circ\text{C}$ unless otherwise specified

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Static Characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	100			V
Zero gate voltage drain current	I_{DSS}	$V_{DS} = 100V, V_{GS} = 0V$			1	μA
Gate-body leakage current	I_{GSS}	$V_{GS} = \pm 20V, V_{DS} = 0V$			± 100	nA
Gate threshold voltage ⁽¹⁾	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	1.0	1.7	2.5	V
Drain-source on-resistance ⁽¹⁾	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 10A$		16.5	22	m Ω
Forward transconductance ⁽¹⁾	g_{FS}	$V_{DS} = 5.0V, I_D = 20A$		51		S
Dynamic characteristics⁽²⁾						
Total gate charge	Q_g	$V_{DS} = 50V, V_{GS} = 10V, I_D = 5A$		15.7		nC
Gate-source charge	Q_{gs}			2.6		
Gate-drain charge	Q_{gd}			4.0		
Input Capacitance	C_{iss}	$V_{DS} = 50V, V_{GS} = 0V, f = 100kHz$		975.3		pF
Output Capacitance	C_{oss}			175		
Reverse Transfer Capacitance	C_{rss}			9.4		
SWITCHING PARAMETERS⁽²⁾						
Turn-on delay time	$t_{d(on)}$	$V_{GS} = 10V, V_{DS} = 50V,$ $R_G = 10\Omega, I_D = 5A$		16.5		ns
Turn-on rise time	t_r			3.7		
Turn-off delay time	$t_{d(off)}$			64.7		
Turn-off fall time	t_f			44		
Source-Drain Diode characteristics⁽¹⁾						
Body diode voltage	V_{SD}	$I_S = 20A, V_{GS} = 0V$			1.3	V


Notes:

1. Pulse Test : Pulse width $\leq 300\mu s$, duty cycle $\leq 0.5\%$.
2. Guaranteed by design, not subject to production testing.
3. The value of $R_{\theta JA}$ is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper, in a still air environment with $T_a = 25\text{ }^\circ\text{C}$.
4. Pd is based on max. junction temperature, using junction-case thermal resistance.

Typical Characteristics




TO-252-2L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.635	0.770	0.025	0.030
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 REF.		0.190 REF.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.712	10.312	0.382	0.406
L1	2.900 REF.		0.114 REF.	
L2	1.400	1.700	0.055	0.067
L3	1.600 REF.		0.063 REF.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.250 REF.		0.207 REF.	

TO-252-2L Suggested Pad Layout




- Note:
1. Controlling dimension: in millimeters.
 2. General tolerance: ± 0.05 mm.
 3. The pad layout is for reference purposes only.

NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.

TO-252-2L Tape and Reel

TO-252 Embossed Carrier Tape




Packaging Description:


TO-252 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 25,00 units per 13" or 33.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
TO-252	6.90	10.50	2.70	Ø1.55	1.75	7.50	4.00	8.00	2.00	16.00

TO-252 Tape Leader and Trailer



TO-252 Reel



Dimensions are in millimeter						
Reel Option	D	D1	D2	W1	W2	I
13" Dia	330.00	100.00	Ø21.00	16.40	21.00	Ø13.00

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
2,500 pcs	13inch	2,500 pcs	340×336×29	25,000 pcs	353×346×365	