

1-1981970-2 ✓ ACTIVE




GRACE INERTIA 2.5

TE Internal #: 1-1981970-2

Rectangular Connector Housings, Wire-to-Wire, 8 Position, .098 in [2.5 mm] Centerline, 2 Row, PBT GF, Plug, Socket, Wire & Cable, GRACE INERTIA 2.5

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Connector Housings > STD Temp Sig GRACE INERTIA Plug



Connector System: **Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **2.5 mm [.098 in]**

Number of Rows: **2**

Housing Material: **PBT GF**

[All STD Temp Sig GRACE INERTIA Plug \(63\)](#)

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Cavities	8
Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
----------------	--------



Contact Type	Socket
--------------	--------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Color	Red
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	PBT GF

Dimensions

Connector Height	11 mm[.511 in]
Product Width	15.2 mm[.598 in]
Product Length	13.7 mm[.539 in]
Row-to-Row Spacing	7.6 mm[.3 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Halogen Free	No
Circuit Application	Signal

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-G7534A-P729
STD Temp Sig GRACE INERTIA Plug



TE Part # CAT-G7534A-C1701
STD Temp Sig GRACE INERTIA Cap




TE Part # 1-2315883-2
GIC2.5W PLUG HOUSING 8POS (2-ROW) RED



TE Part # 2315883-1
GIC2.5W PLUG HOUSING 8POS (2-ROW) NAT

Also in the Series | GRACE INERTIA 2.5




Connector Contacts(6)



Connector Hardware(7)



PCB Headers & Receptacles(138)



Rectangular Connector Housings(49)




Rectangular Power Connectors(35)



Wire-to-Board Connector Assemblies & Housings(46)

Customers Also Bought



TE Part #176773-5
FF 250 CAP HSG 3P NYLON NAT



TE Part #2-1565084-3
GRACE INERTIA CONNECTOR 3.5 6P



TE Part #2-2232571-3
GIC 2.5 W PLUG HSG 3P BLUE



CRIMPER REPRESENTATION ONLY
TE Part #1-1803260-3
CRIMPER, INSULATION F PREMIUM



TE Part #1-2232568-2
GIC 2.5 W PLUG HSG 2P RED




TE Part #2232568-1
GIC 2.5 W PLUG HSG 2P NATURAL



TE Part #2232571-1
GIC 2.5 W PLUG HSG 3P NATURAL



TE Part #913699-2
BLADE,SHEAR



TE Part #1-172127-1
FF 250 REC HSG 1P NYLON NAT



TE Part #1-172128-1
FF 250 PLUG HSG 1P NYLON NAT

Documents

Product Drawings

GIC2.5W PLUG HOUSING 8POS (2-ROW) RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1981970-2_E_c-1-1981970-2-e.2d_dxf.zip

1-1981970-2

Rectangular Connector Housings, Wire-to-Wire, 8 Position, .098 in [2.5 mm]
Centerline, 2 Row, PBT GF, Plug, Socket, Wire & Cable, GRACE INERTIA 2.5



English

Customer View Model

[ENG_CVM_CVM_1-1981970-2_E_c-1-1981970-2-e.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1981970-2_E_c-1-1981970-2-e.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English