

2-1903414-2 ✓ ACTIVE




GRACE INERTIA 9.0

TE Internal #: 2-1903414-2

Rectangular Power Connectors, Housing, Plug, Wire-to-Board, 3 Position, 9 mm [.354 in] Centerline, Wire & Cable, UL 94V-0, GRACE INERTIA 9.0

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors > Glow Wire GRACE INERTIA Plug



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **9 mm [.354 in]**

[All Glow Wire GRACE INERTIA Plug \(78\)](#)

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Power Positions	3
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------



Contact Features

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	20 A
Contact Retention Within Housing	With
Contact Type	Receptacle
Contact Mating Area Plating Material Thickness	.8 μm [31.5 μin]

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	9 mm [.354 in]
Housing Color	Blue
Housing Material	Nylon 6/6 GF

Dimensions

Connector Height	22.9 mm
Product Length	26.4 mm
Wire Size	2427 – 7144 CMA

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2232563-1
GHC 9.0MM 3POS TPA



TE Part # CAT-G7534-R2435
GRACE INERTIA Receptacle




TE Part # 2-1903415-1
GHC 9.0 3POS HDR ASSY BLUE

Also in the Series | GRACE INERTIA 9.0



Connector Hardware(1)



Rectangular Power Connectors(9)


Customers Also Bought



TE Part #2-2232875-1
Glow Wire GRACE INERTIA Plug



TE Part #3-1630019-1
HSC200 1K8 5%



TE Part #1586106-3
3P RCPT VAL-U-LOK SR V0



TE Part #172167-1
4 CIR UNIV M-N-L PLUG



TE Part #1-770902-0
MINI UMNL SOK 26-22 AWG AU



TE Part #1747995-2
GHC EYELET 6.2 3POS PLUG
HOUSING RED



TE Part #2232112-1
250 FASTON,REC.,18-14 AWG,TPBR



TE Part #350638-4
MNL SOK L/P

Documents

Product Drawings

[GHC 9.0 3POS PLUG HSG BLUE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1903414-2_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1903414-2_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1903414-2_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English