


**TUNING FORK CRYSTAL IN SMD 2.0x1.2mm CERAMIC SEAM SEAL PACKAGE.**
**PRODUCT FEATURES**


- Small dimensions 2.0x1.2x0.6mm with 2 solder pads.
- Highly reliable vacuum seam sealed ceramic package.
- Tight tolerances available.
- ROHS compliant, LEAD-FREE and HALOGEN-FREE.

**APPLICATIONS**

- Mobil communication
- Handheld equipment

**PRODUCT PHOTO (NOT IN SCALE)**

**PRODUCT SPECIFICATIONS**

PARAMETER	3121M	CONDITIONS / REMARKS
Nominal frequency range	32.768kHz	
Crystal mode	Fundamental	
Frequency tolerance	±20ppm / ±30ppm / ±50ppm	Other options available.
Stability over temperature	-0.04ppm/Δ°C <sup>2</sup> MAX	Parabolic coefficient.
Operating temperature range	-40 to +85°C	Other options available.
Turning point temperature	25±5°C	
Equivalent series resistance	<90kΩ	At 12.5pF ESR<80kΩ
Shunt capacitance (TYP)	1.3pF	
Motional capacitance (TYP)	5.0fF	
Load capacitance	7pF / 9pF / 12.5pF	Please specify.
Drive level	0.1μW TYP / 0.5μW MAX	
Aging per year	±3ppm	At +25°C
Storage temperature range	-50 to +100°C	

**PACKAGE OUTLINE / DIMENSIONS**

**PACKAGING INFORMATION**

- Tape & Reel compliant to EIA-481.
- Embossed carrier width 12mm.
- Component pitch in carrier 4mm.
- Reel diameter 180mm.
- QTY per reel: 3,000pcs MAX.

**RECOMMENDED REFLOW PROFILE**
