

2320927-1 ✓ ACTIVE

AMP | AMPSEAL 16

TE Internal #: 2320927-1

Housing for Male Terminals, Wire-to-Wire / Wire-to-Device, 3  
Position, .177 in [4.5 mm] Centerline, Sealable, Gray, Wire & Cable,  
AMPSEAL 16

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > AMPSEAL 16 Housings



Connector System: **Wire-to-Device, Wire-to-Wire**

Number of Positions: **3**

Connector & Housing Type: **Housing for Male Terminals**

Centerline (Pitch): **4.5 mm [ .177 in ]**

Sealable: **Yes**

[All AMPSEAL 16 Housings \(226\)](#)

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Device, Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

### Configuration Features

Blank Cavity Position	0
Number of Positions	3
Number of Rows	1

### Electrical Characteristics



Operating Voltage	250 VAC
-------------------	---------

Nominal Voltage Architecture	12 V
------------------------------	------

### Body Features

Cable Exit Angle	180°
------------------	------

Primary Product Color	Gray
-----------------------	------

Connector & Keying Code	1
-------------------------	---

### Contact Features

Contact Size	Size 16
--------------	---------

Contact Type	Pin
--------------	-----

Mating Pin Diameter	1.59 mm [.062 in]
---------------------	-------------------

Contact Current Rating (Max)	13 A
------------------------------	------

### Mechanical Attachment

Terminal Position Assurance	Yes
-----------------------------	-----

Strain Relief	Add By Accessory
---------------	------------------

Mating Alignment Type	Keyed
-----------------------	-------

Mating Alignment	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Housing Material	PBT GF
------------------	--------

Centerline (Pitch)	4.5 mm [.177 in]
--------------------	------------------

### Dimensions

Connector Height	19.15 mm [.754 in]
------------------	--------------------

Product Width	24.1 mm [.949 in]
---------------	-------------------

Product Length	47.55 mm [1.872 in]
----------------	---------------------

Row-to-Row Spacing	0 mm [0 in]
--------------------	-------------

### Usage Conditions

Operating Temperature (Max)	150 °C [302 °F]
-----------------------------	-----------------

Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power, Signal
---------------------	---------------

### Industry Standards

Degree of Protection	IP67
----------------------	------



UL Flammability Rating UL 94V-0

**Packaging Features**

Packaging Method Box

**Other**

Serviceable Yes

Connector Position Assurance Capable Yes

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006 
 Current ECHA Candidate List: JUNE 2023 (235)  
 Candidate List Declared Against: JUNE 2023 (235)  
 SVHC > Threshold:  
 Octamethylcyclotetrasiloxane (D4) (.5% in Component part)  
 Decamethylcyclopentasiloxane (D5) (.5% in Component part)  
 Dodecamethylcyclohexasiloxane (D6) (.5% in Component part)

**Article Safe Usage Statements:**  
 Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not reviewed for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2320933-1  
3POS,AMPSEAL 16,SOC HSG ASSY, SLD,COD 1



TE Part # CAT-AM7801-T273  
Contacts: Size 16, 13A




TE Part # 776363-1  
SEALING PLUG, SZ 16 CAVITY




TE Part # 1924579-1  
PIN CONTACT AU PLATED - loose piece


### Also in the Series | AMPSEAL 16




Automotive Connector Caps & Covers (1)




Automotive Connector Locks & Position Assurance(2)




Automotive Housings(244)




Automotive Terminals(33)



Connector Backshells(84)




Connector Seals & Cavity Plugs(4)



Data Connectivity Headers(2)



Data Connectivity Housings(3)



Other Automotive Connector Accessories(11)

### Customers Also Bought



TE Part #788189-2  
CPC 17-3 RCPT ASY, REV SEX



TE Part #2-330648-1  
PIDG 22-16 22-18 MIL R 4; TAPE



TE Part #2177090-3  
STEEL, OUTER FERRULE, 8MM HV,  
25SQMM



TE Part #1-1633961-2  
CRIMPER, INSULATION F PREMIUM  
25SQMM




TE Part #1587940-3  
CABLE SEAL RETAINER, SIZE C




TE Part #2103013-3  
CABLE SEAL RETAINER, SIZE 2, OR,  
HVA280



TE Part #2208669-3  
8MM HV, CONTACT, ASSY



TE Part #4-1633932-0  
ANVIL, COMBINATION



TE Part #464291-5  
ANVIL, SAND-BLASTED 12-10



TE Part #YHV280-2PM-P-4MM-B  
HVA280-2pmm, pass, 4sqmm, Key B

## Documents

### Product Drawings

[3POS, AMPSEAL 16, PIN HSG ASSY, SLD, COD 1](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2320927-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2320927-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2320927-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications



## Application Specification

English