

5-1418760-3 ✓ ACTIVE

AMP | MCON Interconnection System


TE Internal #: 5-1418760-3

Automotive Terminals, Tab, Mating Tab Width 1.15 mm [.045 in],
Tab Thickness .6 mm [.024 in], 20 – 18 AWG Wire Size, MCON
Interconnection System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > MCON Receptacle and Tab



Terminal Type: **Tab**

Mating Tab Width: 1.15 mm [.045 in]

Mating Tab Thickness: .6 mm [.024 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: 20 – 18 AWG

[All MCON Receptacle and Tab \(99\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	1.15mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Crimp Type	F-Crimp
Terminal Type	Tab
Mating Tab Width	1.15 mm [.045 in]
Mating Tab Thickness	.6 mm [.024 in]
Interface Plating	Silver (Ag)



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.4 – 1.9 mm [.055 – .075 in]
Wire Size	.5 – .75 mm ²
Wire Size Search	18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F]
Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]

Operation/Application

Conforms to KOMAX Automatic Component Insertion Guideline	Yes, per Version 5.0 (March 2018)
Compatible With Wire Base Material	Copper

Industry Standards

Compatible With Agency/Standards Products	LV214
---	-------

Packaging Features

Packaging Quantity	8000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)









Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 5-1579007-3 EXTRACTION TOOL</p>	 <p>TE Part # 1-2371113-1 3POS, DIA 4MM, PIN HSG ASSY, SLD, COD A</p>	 <p>TE Part # 1-2371113-2 3POS, DIA 4MM, PIN HSG ASSY, SLD, COD B</p>	 <p>TE Part # 2-2371113-2 2POS, DIA 4MM, PIN HSG ASSY, SLD, COD B</p>
 <p>TE Part # 2-2371113-3 2POS, DIA 4MM, SOC HSG ASSY, SLD, COD C</p>	 <p>TE Part # 2371113-2 3POS, DIA 4MM, PIN HSG ASSY, SLD, COD B</p>	 <p>TE Part # 2371113-3 3POS, DIA 4MM, PIN HSG ASSY, SLD, COD C</p>	 <p>TE Part # 7-1452656-3 MCON 1.2 LL REC SRC AG</p>




TE Part # CAT-LMPH9507
Low & Medium Power Header



TE Part # 2-2371113-1
2POS,DIA 4MM,PIN HSG ASSY,SLD, COD A



TE Part # 2151300-1
OCEAN_2.0_APPLICATION-S-055F072SP



TE Part # 2151300-2
OCEAN_2.0_APPLICATION-S-055F072SP



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 2371113-1
3POS,DIA 4MM,PIN HSG ASSY,SLD, COD A



TE Part # 2382874-1
16POS,1.2X0.63,TAB HSG ASSY, UNSLD,COD A



TE Part # 2382874-2
16POS,1.2X0.63,TAB HSG ASSY, UNSLD,COD A



TE Part # 2382874-3
16POS,1.2X0.63,TAB HSG ASSY, UNSLD,COD A



TE Part # 2382874-4
16POS,1.2X0.63,TAB HSG ASSY, UNSLD,COD A




TE Part # 2382878-1
3POS,1.2X0.63,TAB HSG,UNSLD,COD A



TE Part # 2382878-3
3POS,1.2X0.63,TAB HSG,UNSLD,COD A


Also in the Series | MCON Interconnection System




Automotive Connector Caps & Covers (21)




Automotive Connector Locks & Position Assurance(11)




Automotive Housings(288)




Automotive Terminals(119)



Connector Seals & Cavity Plugs(11)



Insertion & Extraction Tools(31)



Other Automotive Connector Accessories(2)



PCB Headers & Receptacles(2)

Customers Also Bought



TE Part #170014-6
FF 110 TAB 20-16AWG PTBR



TE Part #2310537-5
PLUG ASSY, KEY E, CPA, HVA280-2PHI, V0



TE Part #2310540-4
HVA280 2P HEADER ASSY, KEY D




TE Part #2310540-5
HVA280 2P HEADER ASSY, KEY E




TE Part #2310541-1
SPLIT HEADER ASSY, KEY A, HVA280, V0




TE Part #2355198-3
HVP800 2P HEADER ASSY




TE Part #1-2388688-3
SUPERSEAL 34P HDR DBL LOCK VER COD 1



TE Part #1-2439022-3
2POS, HYBRID, HDR ASSY, 180DEG, COD 3



TE Part #2371688-2
2POS, TAB2.8X0.8, HDR ASSY, 90DEG, HVA280 RA



TE Part #2415527-2
2POS, HYBRID, HDR ASSY, 180DEG, COD 2, CSJ18

Documents

Product Drawings

[MCON 1.2 LL TAB STC AG](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_5-1418760-3_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-1418760-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1418760-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



MCON Interconnection System

English

Product Specifications

Application Specification

English

Application Specification

English