


APHF1608LSEEQBDZGKC





DESCRIPTIONS

- The Hyper Red source color devices are made with AIGaInP on GaAs substrate Light Emitting Diode
- The Blue source color devices are made with InGaN Light Emitting Diode
- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.6 x 0.8 mm SMD LED, 0.5 mm thickness
- Low power consumption
- Package in 8mm tape on 7" diameter reel, 4000 pcs / reel
- · Can produce any color in visible spectrum, including white light
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




SELECTION GUIDE





PACKAGE DIMENSIONS












RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)





- 1. All dimensions are in millimeters (inches). 2. Tolerance is ±0.15(0.006") unless otherwise noted
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

Part Number	Emitting Color		lv (mcd) @ 2mA ^[2]		Viewing Angle ^[1]	
Fait Number	(Material)	Lens Type	Min.	Тур.	201/2	
	Hyper Red (AlGaInP)	Water Clear	4	15	140°	
APHF1608LSEEQBDZGKC	Blue (InGaN)		4	10		
-	Green (InGaN)		50	90		

Notes

1, 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 Luminous intensity / luminous flux: +/-15%.
 Luminous intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Damastar	Querra ha al		Value		Unit
Parameter	Symbol	Emitting Color	Тур.	Typ. Max.	
Wavelength at Peak Emission I_F = 2mA	λ _{peak}	Hyper Red Blue Green	630 460 515	-	nm
Dominant Wavelength I_F = 2mA	λ_{dom} ^[1]	Hyper Red Blue Green	621 465 525	-	nm
Spectral Bandwidth at 50% Φ REL MAX I_{F} = 2mA	Δλ	Hyper Red Blue Green	20 25 35	-	nm
Capacitance	С	Hyper Red Blue Green	25 100 45	-	pF
Forward Voltage $I_F = 2mA$	V _F ^[2]	Hyper Red Blue Green	1.8 2.65 2.65	2.1 3.1 3.1	V
Reverse Current ($V_R = 5V$)	I _R	Hyper Red Blue Green	-	10 50 50	μA
Temperature Coefficient of λ_{peak} I_F = 2mA, -10°C $\leq T \leq 85°$ C	TC _{λpeak}	Hyper Red Blue Green	0.13 0.04 0.05	-	nm/°C
Temperature Coefficient of λ_{dom} I_F = 2mA, -10°C $\leq T \leq 85°C$	TC _{λdom}	Hyper Red Blue Green	0.06 0.03 0.03	-	nm/°C
Temperature Coefficient of $~V_F$ I_F = 2mA, -10°C \leq T \leq 85°C	TCv	Hyper Red Blue Green	-1.9 -2.9 -2.9	-	mV/°C

Notes:

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C


Parameter	Symbol	Value			Unit
i didileter		Hyper Red	Blue	Green	Unit
Power Dissipation	P _D ^[1]	75	80	82	mW
Reverse Voltage	V _R	5	5	5	V
Junction Temperature	Tj	115	115	115	°C
Operating Temperature	T _{op}	-40 to +85			°C
Storage Temperature	T _{stg}	-40 to +85			°C
DC Forward Current	۱ _۶ ^[1]	30	20	20	mA
Peak Forward Current	I _{FM} ^[2]	195	100	100	mA
Electrostatic Discharge Threshold (HBM)	-	3000	250	450	V
Thermal Resistance (Junction / Ambient)	R _{th JA} ^[3]	730	720	700	°C/W
Thermal Resistance (Junction / Solder point)	R _{th JS} ^[3]	610	620	590	°C/W

Notes:
1. The maximum ratings are valid for the case of lighting a single chip When two chips are lit at the same time, each chip should be driven at a current lower than 50% of the absolute maximum ratings When three chips are lit at the same time, each chip should be driven at a current lower than 30% of the absolute maximum ratings
2. 1/10 Duty Cycle, 0.1ms Pulse Width.
3. R_{th, ds}, R_{th, ds}, Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad).
4. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.


Kingbright

APHF1608LSEEQBDZGKC

TECHNICAL DATA



SPATIAL DISTRIBUTION





Luminous intensity normalised at

HYPER RED

BLUE


GREEN







Forward Current Derating Curve 50 Permissible forward current (mA) 40 30 20 10 0 0 20 40 60 80 100 Ambient temperature (°C)

Luminous Intensity vs. Ambient Temperature









Forward current (mA)

Forward Current Derating Curve




Luminous Intensity vs. Ambient Temperature




Forward Current vs. Forward Voltage 10 T_a = 25 °C 8 Forward current (mA) 6 4

2

0




Luminous Intensity vs. Forward Current 10 T_a = 25 °C 8 6 at 2 mA 4 2 0 0 2 4 6 8 10 Forward current (mA)



Ambient Temperature 2.5 2.0


Luminous Intensity vs.



Kingbright

APHF1608LSEEQBDZGKC

REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes:




Notes: 1. Don't cause stress to the LEDs while it is exposed to high temperature. 2. The maximum number of reflow soldering passes is 2 times. 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.


PACKING & LABEL SPECIFICATIONS




REEL DIMENSION (units : mm)

TAPE SPECIFICATIONS (units : mm)







PRECAUTIONARY NOTES

(SP) XXXXXXXXXXX

- The information included in this document reflects representative usage scenarios and is intended for technical reference only
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer 2 to the latest datasheet for the updated specifications.
- 3 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits. Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- 4 liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright. 5
- All design applications should refer to Kingbright application notes available at https://www.K Votes
- 6