

POWER INDUCTOR


- RoHS Compatible (RoHS6)
- Termination finished: Sn
- Operate temperature range: -40°C to +125°C (Including coil' self temperature rise)
- Storage temperature range : -40° C to $+125^{\circ}$ C



Electrical Specifications @25℃				
Part Number	OCL (uH) @100KHz, 0.25V	DCR (mΩ) ± 30%	Isat(A)	Irms(A)
	S-F	S-F	S-F	S-F
MDRH6045S1681M	$680 \pm 20\%$	3700	0.40	0.30

- The saturation current value (Isat) is the DC current value having inductance decrease down to 30% max. (at 25°C)
- The temperature rise current value (Irms) is the DC current value having temperature increase up to 40°C. (at 25°C)
- The rated current as listed is either the saturation current (Isat)or the temperature rise current (Irms) depending on which value is lower.


MECHANICAL(Unit: mm)



NOTE:

- 1.Unless otherwise specified all tolerances are: tipical.
- 2."S" is winding start,"F" is winding finish.
- 3.Add "S" and "F" on the side of lead wire, in order to distinguish the direction of S-F, therefore the number "1" of marking "681" corresponds to the start of the winding.

SCHEMATICS



PAN SIZE: 1500PCS/REEL UNIT WEIGHT: 0.6g